

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	GVAN
Product or component type	Auxiliary contact block
Product compatibility	GV3L GV2LE GV2RT GV2ME GV2L GV2P GV3P
Mounting location	Left side
Pole contact composition	1 NO + 1 NC
Connections - terminals	Control circuit: spring terminals 1 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end Control circuit: spring terminals 2 cable 0...0 in ² (0.75...2.5 mm ²) - cable stiffness: flexible - without cable end

Complementary

[Ui] rated insulation voltage	600 V - conforming to UL 508 690 V - conforming to IEC 60947-1 600 V - conforming to CSA C22.2 No 14
System Voltage	48...690 V AC 24...240 V DC
[Ith] conventional free air thermal current	6 A
Protection type	GB2CB... circuit breaker rating according to operational current for Ue ≤ 415 V GG fuse ≤ 10 A
Minimum switching current	5 mA
Minimum switching voltage	17 V
Rated operational power in VA	300 VA at 48 V AC-15 - electrical durability: 100000 cycles 400 VA at 690 V AC-15 - electrical durability: 100000 cycles 500 VA at 110...127 V AC-15 - electrical durability: 100000 cycles 500 VA at 500 V AC-15 - electrical durability: 100000 cycles 650 VA at 440 V AC-15 - electrical durability: 100000 cycles 720 VA at 230...240 V AC-15 - electrical durability: 100000 cycles 850 VA at 380...415 V AC-15 - electrical durability: 100000 cycles
Rated operational power in W	120 W at 240 V DC-13 - electrical durability: 100000 cycles 140 W at 110 V DC-13 - electrical durability: 100000 cycles 140 W at 24 V DC-13 - electrical durability: 100000 cycles 180 W at 60 V DC-13 - electrical durability: 100000 cycles 240 W at 48 V DC-13 - electrical durability: 100000 cycles
Height	3.5 in (89 mm)
Width	0.37 in (9.3 mm)
Depth	2.6 in (66 mm)

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901494911
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5
Returnability	N
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0711 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAN113](#)