



## Main

|                               |                                                                |
|-------------------------------|----------------------------------------------------------------|
| Range of Product              | Telemecanique Limit switches XC Standard                       |
| Series name                   | Standard format                                                |
| Product or Component Type     | Limit switch                                                   |
| Device short name             | XCKN                                                           |
| Sensor design                 | Compact                                                        |
| Body type                     | Fixed                                                          |
| Head type                     | Rotary head                                                    |
| Material                      | Plastic                                                        |
| Body Material                 | Plastic                                                        |
| Head material                 | Plastic                                                        |
| Fixing Mode                   | By the body                                                    |
| Movement of operating head    | Rotary                                                         |
| Type of operator              | Spring return roller lever thermoplastic roller diameter 50 mm |
| Type of approach              | Lateral approach, 2 directions                                 |
| Cable entry                   | 1 entry tapped for Pg 11 cable gland                           |
| Number of poles               | 2                                                              |
| Contacts type and composition | 2 NC                                                           |
| Contact operation             | Slow-break, simultaneous                                       |
| Sale per indivisible quantity | 20                                                             |

## Complementary

|                                        |                                                                                                                                                                                                                      |
|----------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Switch actuation                       | By 30° cam                                                                                                                                                                                                           |
| Electrical connection                  | Screw-clamp terminals 1 x 0.34...2 x 1.5 mm <sup>2</sup>                                                                                                                                                             |
| Contacts insulation form               | Zb                                                                                                                                                                                                                   |
| Positive opening                       | With                                                                                                                                                                                                                 |
| Positive opening minimum torque        | 1.33 lbf.in (0.15 N.m)                                                                                                                                                                                               |
| Minimum torque for tripping            | 0.89 lbf.in (0.1 N.m)                                                                                                                                                                                                |
| Maximum actuation speed                | 4.92 ft/s (1.5 m/s)                                                                                                                                                                                                  |
| Contact code designation               | A300, AC-15 (Ue = 240 V), Ie = 3 A 10 A EN/IEC 60947-5-1 appendix A<br>R300, DC-13 (Ue = 250 V), Ie = 0.1 A EN/IEC 60947-5-1 appendix A                                                                              |
| [Ui] rated insulation voltage          | 300 VUL 508<br>500 V 3)IEC 60947-1<br>300 VCSA C22.2 No 14                                                                                                                                                           |
| [Uimp] rated impulse withstand voltage | 6 kV IEC 60664<br>6 kV IEC 60947-1                                                                                                                                                                                   |
| Short-circuit protection               | 10 A cartridge fuse gG                                                                                                                                                                                               |
| Electrical durability                  | 5000000 Cycles, DC-13, 120 V 60 cyc/mn 0.5 IEC 60947-5-1 appendix C<br>5000000 Cycles, DC-13, 24 V 60 cyc/mn 0.5 IEC 60947-5-1 appendix C<br>5000000 cycles, DC-13, 48 V, 4 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C |
| Mechanical durability                  | 10000000 cycles                                                                                                                                                                                                      |
| Width                                  | 1.18 in (30 mm)                                                                                                                                                                                                      |
| Height                                 | 4.96 in (126 mm)                                                                                                                                                                                                     |
| Depth                                  | 1.85 in (47 mm)                                                                                                                                                                                                      |

|                               |                        |
|-------------------------------|------------------------|
| Net Weight                    | 0.24 lb(US) (0.11 kg)  |
| Terminals description ISO n°1 | (21-22)NC<br>(11-12)NC |

## Environment

|                                       |                                                                 |
|---------------------------------------|-----------------------------------------------------------------|
| Shock resistance                      | 15 gn 11 ms IEC 60068-2-27                                      |
| Vibration resistance                  | 15 gn 10...500 Hz)IEC 60068-2-6                                 |
| IP degree of protection               | IP65 conforming to IEC 60529                                    |
| IK degree of protection               | IK04 EN 50102                                                   |
| Overvoltage category                  | Class II IEC 61140<br>Class II NF C 20-030                      |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                      |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                      |
| Protective treatment                  | TC                                                              |
| Product Certifications                | CCC<br>UL<br>CSA                                                |
| Standards                             | UL 508<br>EN/IEC 60204-1<br>CSA C22.2 No 14<br>EN/IEC 60947-5-1 |

## Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 22435 - LIMIT SWITCHES,TYPE XCM |
| Discount Schedule     | T                               |
| GTIN                  | 3389119034388                   |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 3.56 oz (101 g)                 |
| Returnability         | No                              |
| Country of origin     | ID                              |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Package 1 Height             | 4.33 in (11 cm)         |
| Package 1 width              | 6.30 in (16 cm)         |
| Package 1 Length             | 12.20 in (31 cm)        |
| Unit Type of Package 2       | BB1                     |
| Number of Units in Package 2 | 20                      |
| Package 2 Weight             | 4.48 lb(US) (2.03 kg)   |
| Package 2 Height             | 4.33 in (11 cm)         |
| Package 2 width              | 6.30 in (16 cm)         |
| Package 2 Length             | 12.20 in (31 cm)        |
| Unit Type of Package 3       | S03                     |
| Number of Units in Package 3 | 60                      |
| Package 3 Weight             | 14.98 lb(US) (6.797 kg) |
| Package 3 Height             | 11.81 in (30 cm)        |
| Package 3 width              | 11.81 in (30 cm)        |
| Package 3 Length             | 15.75 in (40 cm)        |


## Offer Sustainability

|                            |                                                                                                                                                                                      |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                                                                                                                                                                  |
| RoHS exemption information |  Yes                                                                                              |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a>                                                    |

Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Dimensions



- (1) 1 tapped entry for Pg 11 cable gland  
(2) Ø: 2 elongated holes Ø 4.3 x 6.3 on 22 mm centres, 2 holes Ø 4.3 on 20 mm centres.

---

## Mounting with Cable Entry

---

### Position of Cable Gland



- (1) Recommended
- (2) To be avoided

---

## Mounting with Rotary Heads and Levers

---

### Type of Cam




- (1) Recommended
- (2) To be avoided

---

## Wiring Diagram

---

2-pole NC + NC Simultaneous, Slow Break



---

## Characteristics of Actuation

---


### Switch Actuation by 30° Cam



---

## Functionnal Diagram

---



■ (2)

□ (3)

(P) Positive opening point

(1) NC contact with positive opening operation

(2) Closed

(3) Open

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCKN2739G11](#)