

# XCSPA893

Safety switch, Telemecanique Safety switches  
XCS, plastic XCSPA, 1 NC + 2 NO, slow break,  
1 entry tapped 1/2" NPT



## Main

|                               |                                              |
|-------------------------------|----------------------------------------------|
| Range of Product              | Telemecanique Safety switches XCS            |
| Product or Component Type     | Safety switch                                |
| Component name                | XCSPA                                        |
| Design                        | Compact                                      |
| Material                      | Plastic                                      |
| Head type                     | Key operated turret head                     |
| Contacts type and composition | 1 NC + 2 NO                                  |
| Contact operation             | Slow-break, break before make                |
| Cable entry                   | 1 entry tapped 1/2" NPT                      |
| Electrical connection         | Terminal 1 x 0.34...2 x 0.75 mm <sup>2</sup> |
| Number of poles               | 3                                            |
| Locking options description   | Without locking of actuator                  |

## Complementary

|                                              |                                                                                                                                                                                                                                                                                         |
|----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Insulation                                   | Double insulated                                                                                                                                                                                                                                                                        |
| Positive opening                             | With NC contact                                                                                                                                                                                                                                                                         |
| Mechanical durability                        | 1000000 cycles                                                                                                                                                                                                                                                                          |
| Positive opening minimum force               | 15 N                                                                                                                                                                                                                                                                                    |
| Minimum actuation speed                      | 0.03 ft/s (0.01 m/s)                                                                                                                                                                                                                                                                    |
| Maximum actuation speed                      | 1.64 ft/s (0.5 m/s)                                                                                                                                                                                                                                                                     |
| [Ie] rated operational current               | 6 A 120 V, AC-15, A300 EN/IEC 60947-5-1<br>3 A 240 V, AC-15, A300 EN/IEC 60947-5-1<br>0.55 A 125 V, DC-13, Q300 EN/IEC 60947-5-1<br>0.27 A 250 V, DC-13, Q300 EN/IEC 60947-5-1                                                                                                          |
| [Ithe] conventional enclosed thermal current | 10 A                                                                                                                                                                                                                                                                                    |
| [Ui] rated insulation voltage                | 300 VUL 508<br>300 VCSA C22.2 No 14<br>400 V 3)IEC 60947-1                                                                                                                                                                                                                              |
| [Uimp] rated impulse withstand voltage       | 4 kV EN/IEC 60947-5-4                                                                                                                                                                                                                                                                   |
| Short-circuit protection                     | 6 A cartridge fuse gG (gl)                                                                                                                                                                                                                                                              |
| Actuator forcible withdrawal rtc             | 10 N                                                                                                                                                                                                                                                                                    |
| Maximum operating rate                       | 10 cyc/mn for maximum durability                                                                                                                                                                                                                                                        |
| Safety level                                 | Can reach category 4 with the appropriate monitoring system and correctly wired EN/ISO 13849-1<br>Can reach PL = e with the appropriate monitoring system and correctly wired EN/ISO 13849-1<br>Can reach SIL 3 with the appropriate monitoring system and correctly wired EN/IEC 61508 |
| Safety reliability data                      | B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear                                                                                                                                                                                            |
| Body Material                                | PA (polyamide)                                                                                                                                                                                                                                                                          |
| Head material                                | PA (polyamide)                                                                                                                                                                                                                                                                          |
| Depth                                        | 1.18 in (30 mm)                                                                                                                                                                                                                                                                         |
| Height                                       | 4.21 in (107 mm)                                                                                                                                                                                                                                                                        |
| Width                                        | 1.18 in (30 mm)                                                                                                                                                                                                                                                                         |
| Net Weight                                   | 0.24 lb(US) (0.11 kg)                                                                                                                                                                                                                                                                   |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company mentioned herein. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                       |                                                                                                      |
|---------------------------------------|------------------------------------------------------------------------------------------------------|
| Standards                             | CSA C22.2 No 14<br>EN/IEC 60947-5-1<br>EN 1088/ISO 14119<br>EN/ISO 12100<br>EN/IEC 60204-1<br>UL 508 |
| Product Certifications                | CSA<br>UL                                                                                            |
| Protective treatment                  | TC                                                                                                   |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C)                                                                           |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                           |
| Vibration resistance                  | 5 gn 10...500 Hz)IEC 60068-2-6                                                                       |
| Shock resistance                      | 10 gn 11 ms IEC 60068-2-27                                                                           |
| Electrical shock protection class     | Class II EN/IEC 61140                                                                                |
| IP degree of protection               | IP67 conforming to EN/IEC 60529 and EN/IEC 60947-5-1                                                 |

## Ordering and shipping details

|                       |                               |
|-----------------------|-------------------------------|
| Category              | 22411-LIMIT SWITCHES,IEC,XCKJ |
| Discount Schedule     | T                             |
| GTIN                  | 3389119028561                 |
| Nbr. of units in pkg. | 1                             |
| Package weight(Lbs)   | 3.88 oz (110.0 g)             |
| Returnability         | No                            |
| Country of origin     | FR                            |

## Packing Units

|                        |                  |
|------------------------|------------------|
| Unit Type of Package 1 | PCE              |
| Package 1 Height       | 1.38 in (3.5 cm) |
| Package 1 width        | 5.12 in (13 cm)  |
| Package 1 Length       | 1.97 in (5 cm)   |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                                                                                                                                                  |
|----------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                                                                                                                                            |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                                                                                                                |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                                                                                                   |
| Mercury free               | Yes                                                                                                                                                                                                                                                                                                                                                                              |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                                                                                                                                              |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                                                                                                                                                    |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                                                                                                                                          |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSPA893](#)