



### Main

Product or Component Type	Separate inductive head
Range of Product	Telemecanique Radio frequency identification XG

### Complementary

Enclosure Material	Nickel Plated Brass
Fixing Mode	By screws
Detector design	Cylindrical
Diameter	0.71 in (18 mm)
Electrical Connection	Connector
ISO thread	M18
[Sn] nominal sensing distance	0.31 in (8 mm)
Net Weight	0.07 lb(US) (0.03 kg)
Shape of legend	Cylindrical
Tag type	Read/write code
Working sensing distance	0.26 in (6.5 mm)

### Environment

Ambient Air Temperature for Storage	-40...185 °F (-40...85 °C)
IP Degree of Protection	IP65
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)

### Ordering and shipping details

Category	22491-SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	00785901332954
Package weight(Lbs)	0.13 lb(US) (0.058 kg)
Returnability	No
Country of origin	FR

### Packing Units

Package 1 Height	0.200 dm
Package 1 width	0.600 dm
Package 1 Length	0.870 dm

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
---------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XGSP181630](#)