

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                               |                                      |
|-------------------------------|--------------------------------------|
| Range of product              | Harmony XB4                          |
| Product or component type     | Head for illuminated selector switch |
| Product compatibility         | Integral LED                         |
| Device short name             | ZB4                                  |
| Bezel material                | Chromium plated metal                |
| Head type                     | Standard                             |
| Mounting diameter             | 0.87 in (22 mm)                      |
| Sale per indivisible quantity | 1                                    |
| Shape of signaling unit head  | Round                                |
| Type of operator              | Spring return right to left          |
| Operator profile              | White standard handle                |
| Operator position information | 2 positions 90°                      |

### Complementary

|                             |                                                                                                                                                                                                                                                                                                                                      |
|-----------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width           | 1.14 in (29 mm)                                                                                                                                                                                                                                                                                                                      |
| CAD overall height          | 1.14 in (29 mm)                                                                                                                                                                                                                                                                                                                      |
| CAD overall depth           | 1.69 in (43 mm)                                                                                                                                                                                                                                                                                                                      |
| Product weight              | 0.08 lb(US) (0.037 kg)                                                                                                                                                                                                                                                                                                               |
| Mechanical durability       | 500000 cycles                                                                                                                                                                                                                                                                                                                        |
| Electrical composition code | M6 2 contacts using single blocks in front mounting with integral LED and transformer<br>M10 2 contacts using single blocks in front mounting with integral LED<br>M3 for 4 contacts using single blocks in front mounting with integral LED<br>M4 for 4 contacts using single and double blocks in front mounting with integral LED |

### Environment

|                                       |                                                                                                                       |
|---------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TH                                                                                                                    |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                            |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C)                                                                                            |
| Overvoltage category                  | Class I conforming to IEC 60536                                                                                       |
| IP degree of protection               | IP69<br>IP67<br>IP66 conforming to IEC 60529<br>IP69K                                                                 |
| NEMA degree of protection             | NEMA 13<br>NEMA 4X                                                                                                    |
| IK degree of protection               | IK06 conforming to IEC 50102                                                                                          |
| Standards                             | EN/IEC 60947-1<br>EN/IEC 60947-5-1<br>EN/IEC 60947-5-4<br>EN/IEC 60947-5-5<br>JIS C 4520<br>UL 508<br>CSA C22.2 No 14 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the company Schneider Electric. This information is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                        |                                                                                                                                                                        |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product certifications | BV<br>CSA<br>DNV<br>GL<br>LROS (Lloyds register of shipping)<br>RINA<br>UL listed                                                                                      |
| Vibration resistance   | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                      |
| Shock resistance       | 30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27 |

### Ordering and shipping details

|                       |                                     |
|-----------------------|-------------------------------------|
| Category              | 22468 - PUSHBUTTONS,22MM(METAL) NEW |
| Discount Schedule     | CS2                                 |
| GTIN                  | 00785901382171                      |
| Nbr. of units in pkg. | 1                                   |
| Package weight(Lbs)   | 0.10000000000000001                 |
| Returnability         | N                                   |
| Country of origin     | FR                                  |

### Offer Sustainability

|                           |                                                                                                                            |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including:                                                               |
| ----- Substance 1         | Nickel compounds, which is known to the State of California to cause cancer, and                                           |
| ----- Substance 2         | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

---

Dimensions

---



Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

| Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board                                                                                                                                                                                                                                       | Connection by Faston Connectors |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------|
|                                                                                                                                                                                                                                                                                                                             |                                 |
| <div> (1) Diameter on finished panel or support<br/> (2) 40 mm min. / 1.57 in. min.<br/> (3) 30 mm min. / 1.18 in. min.<br/> (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm <math>_{0}^{+0.4}</math> / 0.88 in. <math>_{0}^{+0.016}</math>)<br/> (5) 45 mm min. / 1.78 in. min.<br/> (6) 32 mm min. / 1.26 in. min. </div> |                                 |

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Panel Cut-outs (Viewed from Installer's Side)



### Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min.

B: 40 mm min.

Dimensions in in.



A: 1.18 in. min.

B: 1.57 in. min.

## General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in:  $T1 + T2 = 0.3 \text{ mm max.}$

## Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm  $\pm$  0.1 / 0.88 in.  $\pm$  0.004
- Orientation of body/fixing collar ZB4 BZ009:  $\pm 2^{\circ} 30'$  (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ 006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB4 BZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB4 BD\*, ZB4 BJ\*, ZB4 BG\*).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Panel  
(2) Printed circuit board

### Mounting of Adapter (Socket) ZBZ 01•

- 1 2 elongated holes for ZBZ 006 screw access
- 2 1 hole  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  for centring adapter ZBZ 01•
- 3 8 ×  $\varnothing 1.2 \text{ mm} / 0.05 \text{ in.}$  holes
- 4 1 hole  $\varnothing 2.9 \text{ mm} \pm 0.05 / 0.11 \text{ in.} \pm 0.002$ , for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes  $\varnothing 2.4 \text{ mm} / 0.09 \text{ in.}$  for clipping in adapter ZBZ 01•

Dimensions An + 18.1 relate to the  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  holes for centring adapter ZBZ 01•.

---

Electrical Composition Corresponding to Code M3


---



---

Electrical Composition Corresponding to Code M4


---



---

Electrical Composition Corresponding to Codes M6 and P2

---



---

Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2

---



---

Legend

---

Single contact



Double contact



Light block



Possible location



## Sequence of Contacts Fitted to 2-position Selector Switch Body

### Position 315°



|          |                                                                                     |                                                                                     |                                                                                   |                                                                                      |                                                                                     |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
| Push     | Position                                                                            | Top                                                                                 |  |  |  |
| Bottom   |  |  |                                                                                   |                                                                                      |                                                                                     |
| Location |                                                                                     | Left                                                                                | Right                                                                             |                                                                                      |                                                                                     |
| State    |                                                                                     | 0                                                                                   | 0                                                                                 |                                                                                      |                                                                                     |
| Contacts | N/O                                                                                 |                                                                                     | open                                                                              | open                                                                                 |                                                                                     |
| N/C      |                                                                                     | closed                                                                              | closed                                                                            |                                                                                      |                                                                                     |

### Position 45°



|          |                                                                                     |                                                                                     |        |                                                                                       |  |
|----------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------|---------------------------------------------------------------------------------------|--|
| Push     | Position                                                                            | Top                                                                                 |        |  |  |
| Bottom   |  |  |        |                                                                                       |  |
| Location |                                                                                     | Left                                                                                | Right  |                                                                                       |  |
| State    |                                                                                     | 1                                                                                   | 1      |                                                                                       |  |
| Contacts | N/O                                                                                 |                                                                                     | closed | closed                                                                                |  |
| N/C      |                                                                                     | open                                                                                | open   |                                                                                       |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZB4BK1413](#)