

# ZB4BW0M15

white light block with body/fixing collar with  
integral LED 230...240V 1NO+1NC

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                               |                                                                                                                                                                                                        |
|-------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range of product              | Harmony XB4                                                                                                                                                                                            |
| Product or component type     | Complete body/contact assembly and light block                                                                                                                                                         |
| Device short name             | ZB4                                                                                                                                                                                                    |
| Fixing collar material        | Zamak                                                                                                                                                                                                  |
| Sale per indivisible quantity | 1                                                                                                                                                                                                      |
| Head type                     | Standard                                                                                                                                                                                               |
| Contacts type and composition | 1 NO + 1 NC                                                                                                                                                                                            |
| Contact operation             | Slow-break                                                                                                                                                                                             |
| Connections - terminals       | Screw clamp terminals: $\leq 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1<br>Screw clamp terminals: $\geq 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN 60947-1 |
| Light source                  | Protected LED                                                                                                                                                                                          |
| Bulb base                     | Integral LED                                                                                                                                                                                           |
| Light block supply            | Direct                                                                                                                                                                                                 |
| Light source colour           | White                                                                                                                                                                                                  |
| [Us] rated supply voltage     | 230...240 V AC, 50/60 Hz                                                                                                                                                                               |

## Complementary

|                                             |                                                                                                                                                                                                                                                                                                                                                                                |
|---------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width                           | 1.18 in (30 mm)                                                                                                                                                                                                                                                                                                                                                                |
| CAD overall height                          | 1.85 in (47 mm)                                                                                                                                                                                                                                                                                                                                                                |
| Terminals description ISO n°1               | (11-12)NC                                                                                                                                                                                                                                                                                                                                                                      |
| Product weight                              | 0.16 lb(US) (0.074 kg)                                                                                                                                                                                                                                                                                                                                                         |
| Contacts usage                              | Standard                                                                                                                                                                                                                                                                                                                                                                       |
| Positive opening                            | With positive opening conforming to EN/IEC 60947-5-1 appendix K                                                                                                                                                                                                                                                                                                                |
| Operating travel                            | 0.06 in (1.5 mm) (NC changing electrical state)<br>0.1 in (2.6 mm) (NO changing electrical state)<br>0.17 in (4.3 mm) (total travel)                                                                                                                                                                                                                                           |
| Operating force                             | 2 N (NC changing electrical state)<br>2.3 N (NO changing electrical state)                                                                                                                                                                                                                                                                                                     |
| Operating torque                            | 0.44 lbf.in (0.05 N.m) (NO changing electrical state)                                                                                                                                                                                                                                                                                                                          |
| Mechanical durability                       | 5000000 cycles                                                                                                                                                                                                                                                                                                                                                                 |
| Tightening torque                           | 7.08...10.62 lbf.in (0.8...1.2 N.m) conforming to EN 60947-1                                                                                                                                                                                                                                                                                                                   |
| Shape of screw head                         | Cross head compatible with Philips no 1 screwdriver<br>Cross head compatible with pozidriv No 1 screwdriver<br>Slotted head compatible with flat Ø 4 mm screwdriver<br>Slotted head compatible with flat Ø 5.5 mm screwdriver                                                                                                                                                  |
| Contacts material                           | Silver alloy (Ag/Ni)                                                                                                                                                                                                                                                                                                                                                           |
| Short-circuit protection                    | 10 A cartridge fuse type gG conforming to EN/IEC 60947-5-1                                                                                                                                                                                                                                                                                                                     |
| [Ith] conventional free air thermal current | 10 A conforming to EN/IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                            |
| [Ui] rated insulation voltage               | 600 V (degree of pollution: 3) conforming to EN 60947-1                                                                                                                                                                                                                                                                                                                        |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to EN 60947-1                                                                                                                                                                                                                                                                                                                                                  |
| [Ie] rated operational current              | 3 A at 240 V, AC-15, A600 conforming to EN/IEC 60947-5-1<br>6 A at 120 V, AC-15, A600 conforming to EN/IEC 60947-5-1<br>0.1 A at 600 V, DC-13, Q600 conforming to EN/IEC 60947-5-1<br>0.27 A at 250 V, DC-13, Q600 conforming to EN/IEC 60947-5-1<br>0.55 A at 125 V, DC-13, Q600 conforming to EN/IEC 60947-5-1<br>1.2 A at 600 V, AC-15, A600 conforming to EN/IEC 60947-5-1 |

|                        |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical durability  | 1000000 cycles, AC-15, 2 A at 230 V, operating rate: <= 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C<br>1000000 cycles, AC-15, 3 A at 120 V, operating rate: <= 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C<br>1000000 cycles, AC-15, 4 A at 24 V, operating rate: <= 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C<br>1000000 cycles, DC-13, 0.2 A at 110 V, operating rate: <= 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C<br>1000000 cycles, DC-13, 0.5 A at 24 V, operating rate: <= 3600 cyc/h, load factor: 0.5 conforming to EN/IEC 60947-5-1 appendix C |
| Electrical reliability | $\Lambda < 10\exp(-6)$ at 5 V, 1 mA in clean environment conforming to EN/IEC 60947-5-4<br>$\Lambda < 10\exp(-8)$ at 17 V, 5 mA in clean environment conforming to EN/IEC 60947-5-4                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Signalling type        | Steady                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Supply voltage limits  | 195...264 V AC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Current consumption    | 14 mA                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Service life           | 100000 h at rated voltage and 25 °C                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Surge withstand        | 1 kV conforming to IEC 61000-4-5                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |

## Environment

|                                       |                                                                                                                                                                        |
|---------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TH                                                                                                                                                                     |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                                                                             |
| Ambient air temperature for operation | -40...158 °F (-40...70 °C)                                                                                                                                             |
| Electrical shock protection class     | Class I conforming to IEC 60536                                                                                                                                        |
| Standards                             | JIS C 4520<br>EN/IEC 60947-5-1<br>UL 508<br>EN/IEC 60947-5-5<br>EN/IEC 60947-1<br>EN/IEC 60947-5-4<br>CSA C22.2 No 14                                                  |
| Product certifications                | CSA<br>UL listed<br>LROS (Lloyds register of shipping)<br>BV<br>DNV<br>RINA<br>GL                                                                                      |
| Vibration resistance                  | 5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6                                                                                                                      |
| Shock resistance                      | 30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27 |
| Resistance to fast transients         | 2 kV conforming to IEC 61000-4-4                                                                                                                                       |
| Resistance to electromagnetic fields  | 9.14 V/yd (10 V/m) conforming to IEC 61000-4-3                                                                                                                         |
| Resistance to electrostatic discharge | 6 kV on contact (on metal parts) conforming to IEC 61000-2-6<br>8 kV in free air (in insulating parts) conforming to IEC 61000-2-6                                     |
| Electromagnetic emission              | Class B conforming to IEC 55011                                                                                                                                        |

## Ordering and shipping details

|                       |                                         |
|-----------------------|-----------------------------------------|
| Category              | 22469 - PUSHBUTTON,22MM ACCESSORIES-NEW |
| Discount Schedule     | CS2                                     |
| GTIN                  | 003389110893533                         |
| Nbr. of units in pkg. | 1                                       |
| Package weight(Lbs)   | 0.5                                     |
| Returnability         | N                                       |
| Country of origin     | FR                                      |

## Offer Sustainability

|                           |                                                                                                                                  |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including:                                                                     |
| ----- Substance 1         | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                    |


## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|



---

Dimensions

---



Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

| Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board                                                                                                                                                                                                                                           | Connection by Faston Connectors                                                    |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------|
|                                                                                                                                                                                                                                                |  |
| <p>(1) Diameter on finished panel or support</p> <p>(2) 40 mm min. / 1.57 in. min.</p> <p>(3) 30 mm min. / 1.18 in. min.</p> <p>(4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm <math>_{0}^{+0.4}</math> / 0.88 in. <math>_{0}^{+0.016}</math>)</p> <p>(5) 45 mm min. / 1.78 in. min.</p> <p>(6) 32 mm min. / 1.26 in. min.</p> |                                                                                    |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZB4BW0M15](#)