

ZBE201

single contact block for head Ø22 1NO early make screw clamp terminal

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Harmony XB5 Harmony XB4
Product or component type	Contact block
Device short name	ZBE
Sale per indivisible quantity	5
IP degree of protection	IP20 IEC 60529
Contacts type and composition	1 NO
Contact operation	Early make
Contact block type	Single
Contacts usage	Staggered contacts
Connections - terminals	Screw clamp terminals $\leq 2 \times 1.5 \text{ mm}^2$ with cable end EN 60947-1 Screw clamp terminals $\geq 1 \times 0.22 \text{ mm}^2$ without cable end EN 60947-1

Complementary

Product weight	0.02 lb(US) (0.011 kg)
Positive opening	Without
Operating travel	0.1 in (2.6 mm) NO changing electrical state 0.17 in (4.3 mm) total travel
Operating force	2.3 N NO changing electrical state
Mechanical durability	10000000 cycles
Tightening torque	7.08...10.62 lbf.in (0.8...1.2 N.m) EN 60947-1
Shape of screw head	Cross pozidriv No 1 Slotted flat Ø 4 mm Slotted flat Ø 5.5 mm
Contacts material	Silver alloy (Ag/Ni)
Short-circuit protection	10 A cartridge fuse gG EN/IEC 60947-5-1
[Ith] conventional free air thermal current	10 A EN/IEC 60947-5-1
[Ui] rated insulation voltage	600 V 3 EN 60947-1
[Uimp] rated impulse withstand voltage	6 kV EN 60947-1
[Ie] rated operational current	3 A 240 V AC-15 A300 EN/IEC 60947-5-1 6 A 120 V AC-15 A300 EN/IEC 60947-5-1 0.1 A 600 V DC-13 Q300 EN/IEC 60947-5-1 0.27 A 250 V DC-13 Q300 EN/IEC 60947-5-1 0.55 A 125 V DC-13 Q300 EN/IEC 60947-5-1
Electrical durability	1000000 cycles AC-15 2 A 230 V $\leq 3600 \text{ cyc/h}$ 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles AC-15 3 A 120 V $\leq 3600 \text{ cyc/h}$ 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles AC-15 4 A 24 V $\leq 3600 \text{ cyc/h}$ 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles DC-13 0.2 A 110 V $\leq 3600 \text{ cyc/h}$ 0.5 EN/IEC 60947-5-1 appendix C 1000000 cycles DC-13 0.5 A 24 V $\leq 3600 \text{ cyc/h}$ 0.5 EN/IEC 60947-5-1 appendix C
Electrical reliability	$\Lambda < 10\exp(-7)$ 1 mA in clean environment EN/IEC 60947-5-4 $\Lambda < 10\exp(-8)$ 5 mA in clean environment EN/IEC 60947-5-4
Mounting of block	Front mounting
Condition of use	Mounting on push-button collar

Electrical composition code	C1 9 C2 7 C3 6 C4 4 C5 5 C6 3 C7 4 C8 2 C9 3 C12 6 M1 6 M2 4 M3 4 M5 2 M6 2 M7 6 M8 4 M9 2 SF1 3 SF2 2 MF1 2 MF2 2 C10 2 M4 2 C13 1
Compatibility code	ZBE

Environment

Protective treatment	TH
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-40...158 °F (-40...70 °C)
Standards	JIS C 4520 EN/IEC 60947-1 EN/IEC 60947-5-1 CSA C22.2 No 14 UL 508 EN/IEC 60947-5-4
Product certifications	CCC RINA LROS (Lloyds register of shipping) DNV GL UL BV GOST CSA
Vibration resistance	5 gn 2...500 Hz IEC 60068-2-6
Shock resistance	30 gn 18 ms half sine wave acceleration IEC 60068-2-27 50 gn 11 ms half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	22469 - PUSHBUTTON,22MM ACCESSORIES-NEW
Discount Schedule	CS2
GTIN	00785901424895
Nbr. of units in pkg.	5
Package weight(Lbs)	0.02
Returnability	Y
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZBE201](#)