



### Overview

#### Presentation

StruxureWare Data Center Expert Enterprise Management Pack provides a complete, surveillance, environmental, and physical infrastructure monitoring solution. Includes: 3 NetBotz Rack Monitor 550, 6 NetBotz Camera Pod 160, 3 NetBotz Rack Sensor Pod 150, 1 NetBotz Vibration Sensor - 12 ft., 1 NetBotz Dry Contact Cable - 15 ft., 1 NetBotz Door Switch Sensor (2) for an APC Rack - 12 ft., 1 NetBotz 0-5V Cable - 15 ft., 1 NetBotz Smoke Sensor - 10 ft., 1 NetBotz Leak Rope Sensor - 20 ft., 1 Beacon, 1 StruxureWare Data Center Expert Enterprise appliance with 25-Node License, 1 StruxureWare Data Center Expert Enterprise Software Support Contract

#### Lead time

Usually Ships within 2 Weeks

### Main

Number of rack unit	2U
Number of cables	2
Communication port protocol	DNS HTTP HTTPS SMTP SMS SNMP SSL TCP/IP
Provided Equipment	1 Node Surveillance License Key 25-Node license key Documentation CD Installation guide

### General

Memory capacity	4GB/5 x 300GB RAID-5 available for data storage
-----------------	---

### Physical

Color	Silver
Height	3.50 in (8.9 cm)
Width	27.99 in (71.1 cm)
Depth	19.02 in (48.3 cm)
Net Weight	55.12 lb(US) (25 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Ambient Air Temperature for Operation	50...95 °F (10...35 °C)
Operating altitude	0...10000 ft
Relative Humidity	5...90 %
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Storage altitude	0...30000 ft (0.00...9144.00 m)
Storage Relative Humidity	5...95 %

## Communications & Management

Communication Network Type	RJ-45 10/100 Base-T USB
----------------------------	----------------------------



## Ordering and shipping details

GTIN	731304246473
Package weight(Lbs)	87.19 lb(US) (39.55 kg)

## Packing Units

Package 1 Height	15.00 in (38.1 cm)
Package 1 width	24.76 in (62.9 cm)
Package 1 Length	35.98 in (91.4 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP9485](#)