

# SRT1500XLA

APC Smart-UPS On-Line, 1500VA, Tower, 120V, 6x 5-15R NEMA outlets, SmartSlot, Extended runtime, W/O rail kit



## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Rated power in W	1350 W
Rated power in VA	1500 VA
Input Connection Type	NEMA 5-15P
Output connection type	6 NEMA 5-15R
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Communication Cable Documentation CD Installation guide Removable support feet USB cable Warranty card

## General

Product web sub-family	High density
Number of power module free slots	0
Number of power module filled slots	0
Redundant	No

## Physical

Color	Black
Height	17.01 in (43.2 cm)
Width	3.35 in (8.5 cm)
Depth	20.00 in (50.8 cm)
Net Weight	48.50 lb(US) (22 kg)
Mounting preference	No preference
Mounting Mode	Rack-mounted with kit
Two post mountable	0

USB compatible	Yes
Mounting position	Vertical

## Input

Input Frequency	40 - 70 Hz auto-sensing
Efficiency at full load	108...150 V 50...150 V 40% load

## Output

Max Configurable Power (Watts)	1350 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
Crest factor	3 : 1
Topology	Double Conversion Online
Waveform Type	Sine wave
Bypass type	Built-in Bypass
Maximum configurable power in VA	1500 VA

## Conformance

Product Certifications	ENERGY STAR V2.0 (USA)
------------------------	------------------------

## Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-4...122 °F (-20...50 °C)
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	50 dBA
Heat dissipation	463 Btu/h
IP degree of protection	IP20

## Batteries & Runtime

Included Battery Modules	1
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Voltage	48V
Battery Charge Power (Watts)	91 W rated
Battery power in VAh	273 VAh runtime
Battery Life	3...5 year(s)
Battery option	SRT48BP 1 819 VAh SRT48BP 2 1365 VAh SRT48BP 3 1910 VAh SRT48BP 4 2456 VAh SRT48BP 5 3002 VAh SRT48BP 6 3548 VAh SRT48BP 8 4640 VAh SRT48BP 10 5731 VAh
Extendable Run Time	0

## Communications & Management

Free slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off (EPO)	Yes

## Surge Protection and Filtering

Surge energy rating	432 J
---------------------	-------

## Ordering and shipping details

GTIN	731304330097
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.69 in (24.6 cm)
Package 1 Width	29.49 in (74.9 cm)
Package 1 Length	23.39 in (59.4 cm)
Package 1 Weight	65.26 lb(US) (29.6 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
ENERGY STAR®	<a href="#">ENERGY STAR UPS V2.0 (USA)</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SRT1500XLA](#)