

SY125K250DL-PDNB

APC Symmetra PX 125kW Scalable to 250kW
with Maintenance Bypass Left, Distribution &
No Batteries



Overview

Presentation	A high-performance, 3-phase, modular, scalable, power protection solution with industry-leading efficiency, capacity, and performance for medium to large data centers and mission critical environments.
Lead time	Usually Ships within 6 Weeks

Main

Main Input Voltage	3 phase 3 phase
Other Input Voltage	400 V 415 V
Main Output Voltage	400 V 3 phase 480 V 3 phase
Other Output Voltage	380 V 415 V
Kw Rating	125000 W
Rated power in VA	125000 VA
Output connector type	Hard Wire 4-wire (3PH + G) 1 Hard Wire 5-wire (3PH + N + G) 1
Battery Type	External battery system
Provided equipment	Assembly service Installation guide Start-Up Service User Manual Web/SNMP Management Card

General

Bypass Voltage Tolerance	+/-10% settable from +/-4/6/8 and 10%
Number of power module free slots	5
Number of power module filled slots	5
Redundant	Yes

Physical

Color	Black
Height	78.39 in (199.1 cm)
Width	62.99 in (160 cm)
Depth	42.13 in (107 cm)
Net Weight	2718.70 lb(US) (1233.18 kg)
USB compatible	No

Input

Input Frequency	40 - 70 Hz auto-sensing
Number of input connectors	1 Hard Wire 4-wire (3PH + G) 1 Hard Wire 5-wire (3PH + N + G)
Efficiency at full load	408...552 V 480 V
Maximum Short Circuit Withstand (Icw)	50 kA
Input Total Harmonic Distortion	Less than 5% for full load
Input protection type	3-pole breaker
Load power factor	0.5 leading to 0.5 lagging
Input Power Factor at Full Load	0.99

Output

Max Configurable Power (Watts)	250000 W
Harmonic distortion	Less than 2%
Output Frequency (sync to mains)	50 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal not synced 50 Hz +/- 0.1 % for 50 Hz nominal not synced 60 Hz sync to mains
Crest factor	Unlimited
Topology	Double Conversion Online
Waveform Type	Sine wave
Output voltage tolerance	+/-1% static and +/- 5% at 100% load step
Output Voltage THD	< 2% linear load and < 3% non-linear load
Overload Operation	10 minutes @ 125% and 60 seconds @ 150%
Bypass type	Built-in Maintenance Bypass Built-in Static Bypass
Efficiency at full load	96 % in battery operation)
Maximum configurable power in VA	500000 VA
Transfer Time	2ms typical

Conformance

Product Certifications	CUL Listed UL Listed
Standards	CSA C22.2 No.107.3-05 EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 OSHPO UL 1778 UL 60950-1

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...3333 ft
Ambient Air Temperature for Storage	-22...158 °F (-30...70 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)
Acoustic level	54 dBA
Heat dissipation	15473 Btu/h
NEMA degree of protection	NEMA 1
IP degree of protection	IP20

Batteries & Runtime

Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	8 h
Battery power in VAH	0 VAh runtime
Extendable Run Time	1

Communications & Management

Free slots	1
Pre-Installed SmartSlot™ Cards	Network management card 2 with environmental monitoring, out of band access and Modbus
Control panel	Touch Screen LCD User Interface
Emergency Power Off (EPO)	Optional

Ordering and shipping details

Package weight(Lbs)	3043.37 lb(US) (1380.45 kg)
---------------------	-----------------------------

Packing Units

Package 1 Height	84.65 in (215 cm)
Package 1 width	73.62 in (187 cm)
Package 1 Length	50.00 in (127 cm)

Offer Sustainability

EU RoHS Directive	Not compliant
Optimized Energy Efficiency	Energy efficient product

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SY125K250DL-PDNB](#)