

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Accessory / separate part type	Cable
--------------------------------	-------

Complementary

Accessory / separate part designation	Bare cable
Accessory / separate part category	Cabling accessories
Cable length	164.04 ft (50 m)
Material	PvR (PVC/NBR) sheath
Color	Matt black
Cable cross section	0 in ² (0.5 mm ²)
Total number of wires	4
Wire insulation material	PVC
Flame retardance	Class C2 conforming to NF C 32-070
[Ue] rated operational voltage	300 V
[Ui] rated insulation voltage	2000 V conforming to NF C 32-201-1
Bending radius	Minimum 3 x external diameter
Tensile strength	10...35 N/mm ²
Hardness	70 shores A (tolerance: +/-5)
Product weight	4.89 lb(US) (2.22 kg)


Environment

Ambient air temperature for operation	-31...194 °F (-35...90 °C)
Ambient air temperature for storage	-40...212 °F (-40...100 °C)
Environmental characteristic	Without silicone Soluble resistant at 90 °C Mineral resistant at 90 °C Synthetic oils at 90 °C Without unmoulding agent

Ordering and shipping details

Category	22499 - SENSORS ACCESSORIES
Discount Schedule	DS2
GTIN	003389110197235
Nbr. of units in pkg.	1
Package weight(Lbs)	4.96
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0601 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XZCB4L0050](#)