

Product availability: Stock - Normally stocked in distribution facility



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Pre-wired connectors
Series name	Application

Complementary

Electrical connection	M12, 8 pins straight female connector
Cable connector fixing	Screw-on
Collar material	Nickel plated brass
Status LED	Without
Cable length	6.56 ft (2 m)
Cable outer diameter	0.25 in (6.4 mm)
Cable composition	8 x 0.34 mm ²
Wire insulation material	PUR
System Voltage	30 V AC 36 V DC
Line Rated Current	2 A
Contact resistance	5000 µOhm
Insulating resistance	1 GΩ
Product weight	0.22 lb(US) (0.1 kg)

Environment

IP degree of protection	IP67 IP69K IP65
Ambient air temperature for storage	-40...194 °F (-40...90 °C)

Ordering and shipping details

Category	22499 - SENSORS ACCESSORIES
Discount Schedule	DS2
GTIN	00785901916079
Nbr. of units in pkg.	1
Package weight(Lbs)	0.01
Returnability	Y
Country of origin	CZ

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2013
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Connections and Schemes

Connectors



GY : Grey
PK : Pink
VT : Violet
BN : Brown
OG : Orange
WH : White
BU : Blue
BK : Black

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XZCP29P12L2](#)