## **GVAE1**

TeSys GV2 and GV3 Manual Starter and Protector, auxiliary contact block, 1 NO or NC, top mount, screw clamp



Product availability: Stock - Normally stocked in distribution facility



Main	
Range	TeSys
Device short name	GVAE
Product or component type	Auxiliary contact block
Product compatibility	GV2P GV3P GV2RT GV2L GV3L GV2LE GV2ME
Mounting location	Front side
Pole contact composition	1 NO/NC
Connections - terminals	Screw clamp terminals 1 cable 00 in² (0.752.5 mm²) - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 00 in² (0.752.5 mm²) - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable 00 in² (0.751.5 mm²) - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 00 in² (12.5 mm²) - cable stiffness: solid Screw clamp terminals 2 cable 00 in² (12.5 mm²) - cable stiffness: solid
Quantity per set	Set of 10

#### Complementary

[Ui] rated insulation voltage	300 V - conforming to UL 508	
	300 V - conforming to CSA C22.2 No 14	
	250 V - conforming to IEC 60947-1	
System Voltage	24240 V AC	
	2460 V DC	
[Ith] conventional free air thermal current	2.5 A	
Protection type	GG fuse 10 A	
	GB2CB06 circuit breaker 10 A	
Mechanical durability	100000 cycles	
Minimum switching current	5 mA	
Minimum switching voltage	17 V	
Rated operational power in VA	120 VA at 110120 V AC-15 - electrical durability: 100000 cycles	
	120 VA at 230240 V AC-15 - electrical durability: 100000 cycles	
	48 VA at 24 V AC-15 - electrical durability: 100000 cycles	
	60 VA at 48 V AC-15 - electrical durability: 100000 cycles	
Rated operational power in W	15 W at 48 V DC-13 - electrical durability: 100000 cycles	
	24 W at 24 V DC-13 - electrical durability: 100000 cycles	
	9 W at 60 V DC-13 - electrical durability: 100000 cycles	
Tightening torque	1.4 N.m - on screw clamp terminals	
Height	0.43 in (11 mm)	
Width	1.77 in (45 mm)	
Depth	1.14 in (29 mm)	
Product weight	0.04 lb(US) (0.02 kg)	

#### Environment

Environmental characteristic Normal environment
-------------------------------------------------

## Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2	
Discount Schedule	l11	
GTIN	00785901343424	
Nbr. of units in pkg.	1	
Package weight(Lbs)	2.99999999999999E-2	
Returnability	Υ	
Country of origin	CZ	

### Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
Product end of life instructions	Need no specific recycling operations	
California proposition 65	WARNING: This product can expose you to chemicals including:	
Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.	
More information	For more information go to www.p65warnings.ca.gov	

#### Contractual warranty

Managati i a ani a al	40	
Warranty period	18 months	

GVAE1

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Schneider Electric:

GVAE1