

Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                           |                         |
|---------------------------|-------------------------|
| Range of product          | Harmony XAC             |
| Product or component type | Pendant control station |
| Device short name         | XACA pistol grip        |

## Complementary

|                                              |                                                                                                                                                                                                         |
|----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Control station type                         | Double insulated                                                                                                                                                                                        |
| Enclosure material                           | Polypropylene                                                                                                                                                                                           |
| Control type                                 | Intuitive                                                                                                                                                                                               |
| Electrical circuit type                      | Control circuit                                                                                                                                                                                         |
| Enclosure type                               | Complete ready for use                                                                                                                                                                                  |
| Control station application                  | Control of single speed hoist motor                                                                                                                                                                     |
| Control station composition                  | 2 push-buttons + 1 emergency stop                                                                                                                                                                       |
| Control button type                          | First pushbutton 1 NC + 1 NO raise, slow<br>Second pushbutton 1 NC + 1 NO lower, slow<br>Stop push-button Ø 30 mm 1 NC latching                                                                         |
| Product compatibility                        | ZB2BE102 for emergency stop<br>ZB2BE102 + ZB2BE101 for each direction                                                                                                                                   |
| Mechanical interlocking                      | With mechanical interlocking                                                                                                                                                                            |
| Control station colour                       | Yellow                                                                                                                                                                                                  |
| Connections - terminals                      | Screw clamp terminals 1 x 2.5 mm <sup>2</sup> with or without cable end<br>Screw clamp terminals 2 x 1.5 mm <sup>2</sup> with or without cable end                                                      |
| Standards                                    | EN/IEC 60204-32<br>EN/IEC 60947-5-1<br>CSA C22.2 No 14<br>UL 508                                                                                                                                        |
| Product certifications                       | UL<br>CSA                                                                                                                                                                                               |
| Protective treatment                         | TH                                                                                                                                                                                                      |
| Ambient air temperature for operation        | -13...158 °F (-25...70 °C)                                                                                                                                                                              |
| Ambient air temperature for storage          | -40...158 °F (-40...70 °C)                                                                                                                                                                              |
| Vibration resistance                         | 15 gn 10...500 Hz IEC 60068-2-6                                                                                                                                                                         |
| Shock resistance                             | 100 gn IEC 60068-2-27                                                                                                                                                                                   |
| Overvoltage category                         | Class II IEC 61140                                                                                                                                                                                      |
| IP degree of protection                      | IP65 IEC 60529                                                                                                                                                                                          |
| IK degree of protection                      | IK08 EN 50102                                                                                                                                                                                           |
| Mechanical durability                        | 1000000 cycles                                                                                                                                                                                          |
| Cable entry                                  | Rubber sleeve with stepped entry 7...15 mm                                                                                                                                                              |
| Contact code designation                     | A600 AC-15 240 V 3 A IEC 60947-5-1 appendix A<br>A600 AC-15 600 V 1.2 A IEC 60947-5-1 appendix A<br>Q600 DC-13 250 V 0.27 A IEC 60947-5-1 appendix A<br>Q600 DC-13 600 V 0.1 A IEC 60947-5-1 appendix A |
| [Ithe] conventional enclosed thermal current | 10 A                                                                                                                                                                                                    |

|                                        |                                                                                                                                                                                                                                                        |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [Ui] rated insulation voltage          | 600 V 3 IEC 60947-1                                                                                                                                                                                                                                    |
| [Uimp] rated impulse withstand voltage | 6 kV IEC 60947-1                                                                                                                                                                                                                                       |
| Contact operation                      | Slow-break                                                                                                                                                                                                                                             |
| Resistance across terminals            | <= 25 MOhm                                                                                                                                                                                                                                             |
| Operating force                        | 13...15 N                                                                                                                                                                                                                                              |
| Short-circuit protection               | 10 A fuse protection cartridge gG                                                                                                                                                                                                                      |
| Rated operational power in W           | 40 W DC-13 1000000 cycles 60 cyc/mn 120 V 0.5 inductive IEC 60947-5-1 appendix C<br>48 W DC-13 1000000 cycles 60 cyc/mn 48 V 0.5 inductive IEC 60947-5-1 appendix C<br>65 W DC-13 1000000 cycles 60 cyc/mn 24 V 0.5 inductive IEC 60947-5-1 appendix C |
| Terminals description ISO n°1          | (11-12)NC<br>(13-14)NO                                                                                                                                                                                                                                 |
| Terminals description ISO n°2          | (11-12)NC                                                                                                                                                                                                                                              |
| Terminal identifier                    | (11-12)NC<br>(13-14)NO                                                                                                                                                                                                                                 |
| Product weight                         | 0.75 lb(US) (0.34 kg)                                                                                                                                                                                                                                  |

### Ordering and shipping details

|                       |                              |
|-----------------------|------------------------------|
| Category              | 22473 - PUSHBUTTON, PENDANTS |
| Discount Schedule     | CS2                          |
| GTIN                  | 00785901770374               |
| Nbr. of units in pkg. | 1                            |
| Package weight(Lbs)   | 0.9100000000000003           |
| Returnability         | N                            |
| Country of origin     | FR                           |

### Offer Sustainability

|                           |                                                                                                                            |
|---------------------------|----------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including:                                                               |
| ----- Substance 1         | Nickel compounds, which is known to the State of California to cause cancer, and                                           |
| ----- Substance 2         | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                              |

### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XACA2053](#)