

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                    |   |
|------------------------------------|---|
| Range of product                   | Harmony XVC6  |
| Product or component type          | Complete pre-wired monolithic tower light               |
| Beacon or indicator bank unit type | 3 illuminated units                                     |
| Sound signalling                   | Without   |
| Mounting diameter                  | 2.36 in (60 mm)   |
| Component name                     | XVC   |
| Light source                       | Green LED steady<br>Orange LED steady<br>Red LED steady |
| [Us] rated supply voltage          | 100...240 V   |
| Supply circuit type                | AC  |

### Complementary

|  |  |
|--|--|
| Material                               | Polycarbonate (illuminated unit)<br>ABS (acrylonitrile butadiene-styrene) (base unit)<br>PBT + ABS (UL94-V0) (top cover) |
| Product mounting                       | On support tube, 22 mm   |
| Cable cross section                    | 0 in <sup>2</sup> (0.33 mm <sup>2</sup> )<br>0 in <sup>2</sup> (0.83 mm <sup>2</sup> )                                   |
| AWG gauge                              | AWG 18<br>AWG 22   |
| Cable length                           | 17.72 in (450 mm)<br>21.65 in (550 mm)   |
| Marking                                | CE   |
| [Uimp] rated impulse withstand voltage | 4 kV   |
| Current consumption                    | 60 mA  |
| Product weight                         | 2.36 lb(US) (1.07 kg)  |
| Height                                 | 26.76 in (679.8 mm)  |

### Environment


|                                       |  |
|---------------------------------------|--|
| Standards                             | EN/IEC 60947-5-1<br>EN/IEC 60947-1   |
| Product certifications                | UL   |
| Protective treatment                  | TC   |
| Ambient air temperature for storage   | -31...158 °F (-35...70 °C)   |
| Ambient air temperature for operation | 14...122 °F (-10...50 °C)  |
| Electrical shock protection class     | Class I conforming to EN/IEC 61140   |
| IP degree of protection               | IP23 in vertical surface installation conforming to EN/IEC 60529<br>IP54 in flat surface installation conforming to EN/IEC 60529 |

### Ordering and shipping details

|                       |                          |
|-----------------------|--------------------------|
| Category              | 22617 - XVC TOWER LIGHTS |
| Discount Schedule     | XV                       |
| GTIN                  | 00785901120926           |
| Nbr. of units in pkg. | 1                        |
| Package weight(Lbs)   | 3.0700000000000003       |

|                   |    |
|-------------------|----|
| Returnability     | N  |
| Country of origin | ID |

### Offer Sustainability

|                                  |  |
|----------------------------------|--|
| Sustainable offer status         | Green Premium product  |
| RoHS (date code: YYWW)           | Compliant - since 0808 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold  |
| Product environmental profile    | Available  |
| Product end of life instructions | Need no specific recycling operations  |
| California proposition 65        | WARNING: This product can expose you to chemicals including:   |
| - - - - - Substance 1            | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.   |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>  |


### Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

## Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

### Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b1 dimension.




| No. of illuminated units | b1 With buzzer (mm) | b1 With buzzer (in.) |
|--------------------------|---------------------|----------------------|
| 1 stage                  | 599.8               | 23.61                |
| 2 stages                 | 639.8               | 25.19                |
| 3 stages                 | 679.8               | 26.76                |
| 4 stages                 | 719.8               | 28.34                |
| 5 stages                 | 759.8               | 29.91                |

---

Pre-assembled and Pre-wired Tower Light

---

Support Tube Mounting



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVC6M3](#)