



Main

Range of Product	Harmony iPC
Product or Component Type	PC panel
Processor name	Atom N270 1.66 GHz L2 cache 512 kB
Chipset type	Intel 945GME 533 MHz
Display size	19 inch
Display colour	16 million colours
Luminance	27.87 fc (300 cd/m²)
Video controller type	Intel Graphics Media Accelerator (GMA) 950, 224 MB
Operating system	MS Windows XP Professional Edition SP3multi-language
Software package	Vijeo Designer run time demo
Bezel material	Aluminium alloy

Complementary

Terminal type	Touchscreen display
Data storage equipment	500 GB enterprise hard disk
Display Type	Active matrix colour TFT LCD with LED backlight
Display Resolution	1280 x 1024 pixels SXGA
View angle horizontal x vertical	160 x 100°
Touch panel	Analogue resistive
Memory type	512 kB SRAM 2 GB RAM DDR3
Type of cooling	Fanless
Integrated connection type	2 Ethernet TCP/IP - RJ45 DVI-I video port - DVI-I COM1 serial link - male SUB-D 9 - RS232C 115 kbit/s COM2 serial link - male SUB-D 9 - RS232C 115 kbit/s 5 USB 2.0 type A 480 Mbit/s)
Port Ethernet	10BASE-T/100BASE-T/1000BASE-T
[Us] rated supply voltage	24 V DC power supply
Supply voltage limits	18...30 V
Line Rated Current	6.7 A
Inrush current	7 A
Power consumption in W	130 W
Material	Treated steel
Display material	Polyethylene sheet
Fixing mode	Enclosure door by fixing kit fasteners included) Panel by fixing kit fasteners included)
Type of Installation	Indoor
Control type	ON/OFF push-button equipment ON and OFF) Push-button reset)
Local signalling	For power LED (multi-colour) For accessing hard disk (DISK) LED (yellow)
Width	18.90 in (480 mm)
Height	14.96 in (380 mm)
Depth	4.49 in (114 mm)
Cut-out dimensions	459.5 (+/- 0.5) x 359.5 (+/- 0.5) x 1.6...10 mm
Net Weight	30.18 lb(US) (13.69 kg)
Main type	Universal

Environment

IP degree of protection	Front panel IP65 EN/IEC 60529
NEMA degree of protection	NEMA 4X front panel
Product certifications	CULus 508 CULus CSA 22-2 No 142 CULus HazLoc Class I Division 2 UL 1604 CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 GOST CE C-tick
Pollution degree	2 EN/IEC 61131-2
Electromagnetic compatibility	Immunity to electromagnetic emissions, class A EN 55022 Immunity to electromagnetic emissions, class A EN 55011 Immunity to high frequency interference EN/IEC 61131-2 Immunity to high frequency interference EN/IEC 61000-4-x
Ambient air temperature for operation	32...122 °F (0...50 °C) vertical installation UL 508 32...113 °F (0...45 °C) vertical installation when using Gigabit Ethernet with HDD storage device UL 508 32...122 °F (0...50 °C) vertical installation EN/IEC 61131-2 32...113 °F (0...45 °C) vertical installation when using Gigabit Ethernet with HDD storage device EN/IEC 61131-2
Ambient air temperature for storage	-4...140 °F (-20...60 °C) IEC 60068-2-2 test Bb -4...140 °F (-20...60 °C) IEC 60068-2-14 test Na
Relative Humidity	10...85 % EN/IEC 60068-2-78 10...85 % EN/IEC 60068-2-30
Operating altitude	6561.68 ft (2000 m) EN/IEC 61131-2
Vibration resistance	1 mm 3...13.2 Hz) continuous EN/IEC 60068-2-6 Fc 0.7 gn 13.2...100 Hz) continuous EN/IEC 60068-2-6 Fc 0.125 gn 5...100 Hz) continuous EN/IEC 60068-2-6 Fc 0.250 gn 5...100 Hz) intermittently EN/IEC 60068-2-6 Fc
Shock resistance	15 gn 11 ms IEC 60068-2-27, Ea tests

Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	3595864143804
Nbr. of units in pkg.	1
Package weight(Lbs)	29.21 lb(US) (13.248 kg)
Returnability	No
Country of origin	AT


Packing Units

Unit Type of Package 1	PCE
Package 1 Height	14.25 in (36.2 cm)
Package 1 width	19.88 in (50.5 cm)
Package 1 Length	23.62 in (60 cm)

Contractual warranty



Warranty	18 months
----------	-----------

Dimensions




K : 12.8 mm / 0.50 in.


Spacing Requirements

Top, Bottom and Rear Sides	Left and Right Sides
 1 Air out 2 Air in	
x1 > 100 mm (3.93 in.) x2 > 50 mm (1.96 in.) x3 > 10 mm (0.39 in.)	

Mounting Orientation



Panel Cut Dimensions



1 Installation panel		
A	B	C
459.5 ± 0.5 mm (18.09 ± 0.02 in.)	359.5 ± 0.5 mm (14.15 ± 0.02 in.)	1.6...10 mm (0.06...0.39 in.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIPUH9D0P01](#)