



## Main

Range of Product	Interface for discrete signals
Product or Component Type	Slim electromechanical input interface module
Contacts type and composition	1 NO
[Uc] control circuit voltage	120...127 V
Control circuit type	AC/DC
Control circuit frequency	60 Hz
Width pitch dimension	0.37 in (9.5 mm)
Maximum [In] rated current	0.016 A
Short-circuit protection	2 A external fuse fast blow
[Ith] conventional free air thermal current	1 A IEC 60947-1
Local signalling	For control signal state green LED
Quantity per Set	Set of 5

## Complementary

Control circuit voltage limits	140 V
Connections - Terminals	Screw clamp terminal
Operating threshold	97 V
Drop-out voltage	25.4 V
Holding Current	2.5 mA
Power dissipation in W	0.73 W
Maximum switching voltage	125 V DC 140 V AC
[Ue] rated operational voltage	<= 100 V DC IEC 60947-5-1 built-in contacts <= 127 V AC IEC 60947-5-1 built-in contacts
Network Frequency	50/60 Hz
[Ie] rated operational current	1 A AC-12 Ue: 127 V 1000000 cycles IEC 60947-5-1 1 A DC-12 Ue: 24 V 1000000 cycles IEC 60947-5-1 1 A DC-13 Ue: 24 V 1000000 cycles IEC 60947-5-1 0.5 A AC-14 Ue: 127 V 1000000 cycles IEC 60947-5-1 0.5 A AC-15 Ue: 127 V 1000000 cycles IEC 60947-5-1
Minimum switching current	1 mA
Minimum switching voltage	5 V
Electrical reliability	1e-008
Operating time	<= 10 ms between energisation of coil and closing of NO contact DC <= 30 ms between de-energisation of coil and closing of NO contact AC <= 30 ms between energisation of coil and closing of NO contact AC <= 6 ms between de-energisation of coil and closing of NO contact DC
Contact bounce time	<= 5 ms
Operating rate in Hz	10 Hz at no-load 0.5 Hz at Ie
Mechanical durability	20000000 cycles
[Ui] rated insulation voltage	250 V VDE 0110 group C 300 V IEC 60947-1
Flame retardance	V0 conforming to UL 94
Cable cross section	0.00...0.01 In <sup>2</sup> (0.27...4 mm <sup>2</sup> ), 1 wire rigid 0.00...0.00 In <sup>2</sup> (0.34...2.5 mm <sup>2</sup> ), 1 or 2 wires flexible with cable end 0.00...0.00 in <sup>2</sup> (0.6...2.5 mm <sup>2</sup> ), 1 or 2 wires flexible without cable end

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Operating position	Any position
Installation category	II IEC 60947-1
Mounting Support	Asymmetrical DIN rail Symmetrical DIN rail Combination rail
Net Weight	0.08 lb(US) (0.035 kg)

## Environment

Immunity to microbreaks	10 ms
Dielectric strength	2000 V between coil circuit and contact circuits 2500 V between wired interface and earth 750 V between open contacts
Standards	IEC 60947-5-1
Product Certifications	UL CSA LROS (Lloyds register of shipping) DNV BV
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TC
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Shock resistance	30 gn 11 ms IEC 60068-2-27
Vibration resistance	3 gn 10...150 Hz)IEC 60068-2-6
Electromagnetic compatibility	1.2/50 µs shock waves immunity test IEC 947-1 Electromagnetic field immunity test, level 3 10 V/m between 27...1000 MHz IEC 61000-4-3 Electrostatic discharge immunity test, level 3 8 kV IEC 61000-4-2 Rapid transients immunity test, level 3 on input/output 1 kV IEC 61000-4-4 Rapid transients immunity test, level 3 on power supply 2 kV IEC 61000-4-4
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C) at Us 23...104 °F (-5...40 °C) unrestricted operation 23...131 °F (-5...55 °C) from 0.85...1.1 Us
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Operating altitude	<= 9842.52 ft (3000 m)
Pollution degree	2 IEC 60947-1

## Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	3389110651454
Nbr. of units in pkg.	1
Package weight(Lbs)	1.52 oz (43 g)
Returnability	No
Country of origin	FR

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.54 in (9 cm)
Package 1 width	2.83 in (7.2 cm)
Package 1 Length	4.21 in (10.7 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Weight	7.58 oz (215 g)
Package 2 Height	3.54 in (9 cm)
Package 2 width	2.83 in (7.2 cm)
Package 2 Length	4.21 in (10.7 cm)
Unit Type of Package 3	S01
Number of Units in Package 3	25
Package 3 Weight	2.87 lb(US) (1.3 kg)
Package 3 Height	5.91 in (15 cm)

Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

## Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Slim Electromechanical Interface Module


Dimensions



## Slim Electromechanical Interface Module

### Example of Application with PLC

Interfacing PLC discrete inputs




ABR 2E\*\*\*\*

- S1 Pushbuttons series contacts
- (1) Processing power supply
- (2) PLC positive logic discrete inputs
- (3) Process power supply
- (4) 2-wire sensors
- (5) 3-wire sensors

## Slim Electromechanical Interface Module

### Circuit Diagram

1 N/O



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ABR2E116F](#)