

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Device short name	LUA1
Product or component type	Auxiliary contact

Complementary

Auxiliary contact composition	1 NO + 1 NC
Signalling function	Indicating rotary knob in ready position Fault signalling
System Voltage	≤ 250 V AC ≤ 250 V DC
[Ui] rated insulation voltage	250 V conforming to CSA 250 V conforming to IEC 60947-5-1 250 V conforming to UL
[Ith] conventional free air thermal current	2.5 A
Minimum switching voltage	17 V
Minimum switching current	5 mA
Product weight	0.07 lb(US) (0.03 kg)
Connections - terminals	Screw clamp terminals

Ordering and shipping details

Category	22399 - TESYS U, ACCESSORIES
Discount Schedule	I11
GTIN	00785901202462
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	Y
Country of origin	CZ

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0721 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LUA1C11](#)