

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XG
Product or component type	Portable diagnostic terminal
RFID diagnostic terminal name	XGST
Processor name	CPU ARM7

Complementary

RFID frequency	13.56 MHz
Terminal use	Diagnostics on compact stations Read / write operations on tags
[Us] rated supply voltage	5 V DC AC external adaptor 3.7 V DC internal battery
Autonomy	8 h
Memory description	Expandable USB memory stick, up to 2 GB Internal data storage Compact Flash, 2 GB Internal RAM RAM/SDRAM, 256 kB
Display type	OLED colour touchscreen
Display size	54 x 95 mm
Pixel resolution	480 x 272 pixels
Status LED	1 LED charging
Communication port support	RS485 non isolated USB
Marking	CE
Product weight	0.65 lb(US) (0.295 kg)

Environment

Product certifications	CE
Ambient air temperature for operation	32...113 °F (0...45 °C)
Ambient air temperature for storage	-4...113 °F (-20...45 °C)
Relative humidity	5...95 %
IP degree of protection	IP40

Ordering and shipping details

Category	22491 - SENS,IDENTIFICATION DEVICE (XGK)
Discount Schedule	DS2
GTIN	003389119081436
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8499999999999998
Returnability	N
Country of origin	FR

Offer Sustainability


California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions

RFID Handheld Terminal



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XGST2020](#)