

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Preventa Safety detection
Product or component type	Safety switch
Component name	XCSLF
Design	Slim
Material	Metal
Head type	Key operated turret head
Contacts type and composition	1 NC + 2 NO
Contact operation	Slow-break, break before make
Solenoid contacts type and composition	1 NC + 2 NO (slow-break, break before make)
Cable entry	3 entries tapped 1/2" NPT
Electromagnet interlocking	Locking on energisation and unlocking on de-energisation of solenoid
[Us] solenoid rated supply voltage	24 V (- 15...10 %)
Electrical connection	Spring terminal, 1 x 1.5 mm ² flexible or solid cable Spring terminal, 2 x 0.5 mm ² flexible cables with 13 mm bared ends
Number of poles	3
Locking options description	With interlocking, locking by solenoid
Local signalling	1 LED orange (actuator withdrawn) 1 LED green (actuator inserted and locked)
Signalling circuit voltage	24 V

Complementary

Positive opening	With NC contact
Supply voltage type	AC/DC
Supply frequency	50/60 Hz
Load factor	1
Signalling circuit type	AC/DC
Mechanical durability	1000000 cycles
Minimum actuation speed	0.03 ft/s (0.01 m/s)
Maximum actuation speed	1.64 ft/s (0.5 m/s)
[Ie] rated operational current	0.55 A at 24 V utilisation category DC-13, R300 conforming to EN/IEC 60947-5-1 0.75 A at 240 V utilisation category AC-15, C300 conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	4 A
Maximum load current	<= 15 A
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 250 V (degree of pollution: 3) conforming to EN/IEC 60947-1 300 V conforming to UL 508
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60947-5-1
Minimum switching current	10 mA at 20 °C
Minimum switching voltage	17 V
Short-circuit protection	4 A cartridge fuse type gG (gl) 6 A type fast blow
Actuator forcible withdrawal rtc	3000 N
Actuator force for extraction	>= 20 N

Resistance to mechanical impact	9.6 J against the partition 6.4 J without partition
Operating rate	10 cyc/mn for maximum durability
Safety level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 conforming to EN/IEC 61508
Safety reliability data	B10d = 5500000 (value given for a life time of 20 years limited by mechanical or contact wear)
Body material	Zamak
Head material	Zamak
Depth	2.01 in (51 mm)
Height	8.07 in (205 mm)
Width	1.73 in (44 mm)
Product weight	2.43 lb(US) (1.1 kg)

Environment

Standards	UL 508 EN 1088/ISO 14119 EN/ISO 13849-1 EN/IEC 60204-1 EN/IEC 62061 EN/IEC 60947-5-1 CSA C22.2 No 14
Product certifications	TÜV UL CSA
Protective treatment	TC
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Vibration resistance	5 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	10 gn 11 ms conforming to IEC 60068-2-27
Electrical shock protection class	Class I conforming to EN/IEC 61140
IP degree of protection	IP66 conforming to EN/IEC 60529 and EN/IEC 60947-5-1 IP67

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003606489413415
Nbr. of units in pkg.	1
Package weight(Lbs)	2.4199999999999999
Returnability	N
Country of origin	ID

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1045 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSLF3535513](#)