

# XVC4M35S

## 40mm Tower ROGPole

## BuzzerFlash100-240VAC



Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	Harmony XVC4
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	3 illuminated units
Sound signalling	Buzzer
Mounting diameter	1.57 in (40 mm)
Device short name	XVC
Component name	XVC
Light source	Green LED steady or flashing Orange LED steady or flashing Red LED steady or flashing
Supply circuit type	AC
Noise level	70...85 dB (continuous or intermittent tone)at 1 m

### Complementary

Material	Polycarbonate (illuminated unit) ABS (acrylonitrile butadiene-styrene) (base unit) PBT + ABS (UL94-V0) (top cover) SGP (chromium-plated) (support tube)
Product mounting	On support tube, 17 mm
Mounting location	On support tube, 17 mm
[Us] rated supply voltage	100...240 V
[Us] rated supply voltage	100...240 V
Cable cross section	0 in <sup>2</sup> (0.83 mm <sup>2</sup> ) 0 in <sup>2</sup> (0.33 mm <sup>2</sup> )
AWG gauge	AWG 22 AWG 18
Cable length	17.72 in (450 mm)
Marking	CE
[Uimp] rated impulse withstand voltage	4 kV
Current consumption	80 mA
Fundamental frequency	2.23 kHz
Flashing frequency	1 Hz
Product weight	1.76 lb(US) (0.8 kg)
Height	25.09 in (637.2 mm)


### Environment

Standards	EN/IEC 60947-1 EN/IEC 60947-5-1
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Electrical shock protection class	Class I conforming to EN/IEC 61140
Overvoltage category	Class I EN/IEC 61140
IP degree of protection	IP23 in vertical surface installation conforming to EN/IEC 60529 IP54 in flat surface installation conforming to EN/IEC 60529

## Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	00785901118831
Nbr. of units in pkg.	1
Package weight(Lbs)	2.2600000000000002
Returnability	N
Country of origin	ID

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0808 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>


## Contractual warranty

Warranty period	18 months
-----------------	-----------

## Pre-assembled and Pre-wired Tower Light with Support Tube Mounting

### Dimensions


Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get b1 dimension.



No. of illuminated units	b1 Without buzzer (mm)	b1 Without buzzer (in.)
1 stage	567.20	22.33
2 stages	602.20	23.71
3 stages	637.20	25.09
4 stages	672.20	26.46
5 stages	707.20	27.84

## Pre-assembled and Pre-wired Tower Light

## Support Tube Mounting



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVC4M35S](#)