

XVPC6G4W

RED STROBE/OFF-WHITE RING 0.6J

120VAC



Main

Range of Product	Harmony XVP Universal
Product or Component Type	Indicator bank
Beacon or indicator bank unit type	Illuminated unit with cream clamping ring
Signalling type	Flashing
Mounting diameter	1.97 in (50 mm)
Component name	XVPC
Material	Polycarbonate and polyamide
Light source	Integral flash discharge tube, red
Bulb type	Flash discharge tube
[Us] rated supply voltage	120 V AC
Flash energy	0.6 J

Complementary

Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end
Marking	CE
[Ui] rated insulation voltage	250 V IEC 60947-1
Nominal voltage limit	0.85...1.1 Un IEC 60947-5-1
Current consumption	<= 20 mA AC
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Flashing frequency	0.6...2 Hz
Service life in hours	1000 h -13...122 °F (-25...50 °C)
CAD overall width	2.20 in (56 mm)
CAD overall height	2.56 in (65 mm)
CAD overall depth	2.20 in (56 mm)
Net Weight	0.25 lb(US) (0.115 kg)

Environment

Product Certifications	cULus
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Electrical shock protection class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
IP degree of protection	IP65 IEC 60529

Ordering and shipping details

Category	22615 - XVP 50MM INDICATING BANKS
Discount Schedule	XV
GTIN	00785901430025
Nbr. of units in pkg.	1
Package weight(Lbs)	0.25 lb(US) (0.11 kg)
Returnability	No
Country of origin	CN

Packing Units

Package 1 Height	0.650 dm
Package 1 width	0.700 dm
Package 1 Length	1.300 dm


Contractual warranty

Warranty	18 months
----------	-----------

Indicator Bank without Audible Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get b dimension.



Number of illuminated units	b in mm	b in in.
1	108	4.25
2	170	6.69
3	232	9.13
4	294	11.57
5	356	14.02

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVPC6G4W](#)