



Main

Range of Product	Harmony iPC
Product or Component Type	PC panel
Processor name	Core 2 Duo P8400 2.26 GHz cache 6 MB
Chipset type	Intel GM45 1.066 GHz
Display size	15 inch
Display colour	16 million colours
Luminance	32.52 fc (350 cd/m²)
Drive type	DVD-RW
Video controller type	Intel Graphics Media Accelerator (GMA) 4500MHD, 384 MB
Operating system	Windows 7 64 bits Ultimatemulti-language
Software package	Vijeo Designer run time demo
Bezel material	Aluminium alloy

Complementary

Terminal type	Touchscreen display
Data storage equipment	500 GB enterprise hard disk
Display Type	Active matrix colour TFT LCD with LED backlight
Display Resolution	1024 x 768 pixels XGA
View angle horizontal x vertical	160 x 100°
Touch panel	Analogue resistive
Memory type	512 kB SRAM 4 GB RAM DDR3
Type of cooling	Fan
Integrated connection type	2 Ethernet TCP/IP - RJ45 DVI-I video port - DVI-I COM1 serial link - male SUB-D 9 - RS232C 115 kbauds) COM2 serial link - male SUB-D 9 - RS232C 115 kbauds) USB 2.0 type A 480 Mbit/s)front panel 4 USB 2.0 type A 480 Mbit/s)top panel
Number of slots	1 PCI 1 PCI express 4x
[Us] rated supply voltage	100...240 V AC power supply
Supply voltage limits	85...265 V
Network frequency	50-60 Hz 47...63 Hz
Line Rated Current	1.6 A
Inrush current	40 A
Power consumption in W	130 W
Display material	Polyethylene sheet
Fixing mode	Enclosure door by fixing kit fasteners included) Panel by fixing kit fasteners included)
Control type	ON/OFF push-button equipment ON and OFF) Push-button reset)
Local signalling	For power multi-colour LED For accessing hard disk (DISK) LED
Width	15.83 in (402 mm)
Height	11.85 in (301 mm)
Depth	6.61 in (168 mm)

Net Weight	26.28 lb(US) (11.92 kg)
Main type	Performance

Environment

IP degree of protection	IP65 EN/IEC 61131-2
NEMA degree of protection	NEMA 4X
Product certifications	CULus 508 CULus CSA 22-2 No 142 CULus HazLoc Class I Division 2 UL 1604 CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 GOST CE C-tick
Pollution degree	2 EN/IEC 61131-2
Electromagnetic compatibility	Immunity to high frequency interference EN/IEC 61131-2 Immunity to high frequency interference EN/IEC 61000-4-x Immunity to electromagnetic emissions EN 55022 Class A Immunity to electromagnetic emissions EN 55011 class A
Ambient air temperature for operation	32...122 °F (0...50 °C) vertical installation UL 508 32...113 °F (0...45 °C) vertical installation when using Gigabit Ethernet with HDD storage device UL 508 32...122 °F (0...50 °C) vertical installation EN/IEC 61131-2 32...113 °F (0...45 °C) vertical installation when using RAID option EN/IEC 61131-2 32...113 °F (0...45 °C) vertical installation when using RAID option UL 508 41...113 °F (5...45 °C) vertical installation when using DVD writer EN/IEC 61131-2 41...113 °F (5...45 °C) vertical installation when using DVD writer UL 508 32...113 °F (0...45 °C) vertical installation when using Gigabit Ethernet with HDD storage device EN/IEC 61131-2
Ambient air temperature for storage	-4...140 °F (-20...60 °C) IEC 60068-2-2 test Bb -4...140 °F (-20...60 °C) IEC 60068-2-14 test Na
Relative Humidity	10...85 % EN/IEC 60068-2-78 10...85 % EN/IEC 60068-2-30 Db
Operating altitude	6561.68 ft (2000 m) EN/IEC 61131-2
Vibration resistance	1 mm 3...13.2 Hz) continuous EN/IEC 60068-2-6 Fc 0.7 gn 13.2...100 Hz) continuous EN/IEC 60068-2-6 Fc 0.125 gn 5...100 Hz) continuous EN/IEC 60068-2-6 Fc 0.250 gn 5...100 Hz) intermittently EN/IEC 60068-2-6 Fc
Shock resistance	15 gn 11 ms IEC 60068-2-27, Ea tests

Ordering and shipping details

Category	22575 - MAGELIS MC3
Discount Schedule	MC3
GTIN	00785901321538
Nbr. of units in pkg.	1
Package weight(Lbs)	26.28 lb(US) (11.92 kg)
Returnability	No
Country of origin	AT


Packing Units

Package 1 Height	13.78 in (350.000 mm)
Package 1 width	15.75 in (400.000 mm)
Package 1 Length	19.69 in (500.000 mm)

Contractual warranty



Warranty	18 months
----------	-----------

Dimensions




K : 28 mm / 1.10 in.


Spacing Requirements

Top, Bottom and Rear Sides	Left and Right Sides
 1 Air out 2 Air in	
x1 > 100 mm (3.93 in.) x2 > 50 mm (1.96 in.) x3 > 10 mm (0.39 in.)	

Mounting Orientation



Panel Cut Dimensions



1 Installation panel		
A	B	C
383.5 + 1/- 0 mm (15.10 + 0.04/- 0 in.)	282.5 + 1/- 0 mm (11.12 + 0.04/- 0 in.)	1.6...10 mm (0.06...0.39 in.)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIPPH7A2701](#)