



Main

Range of Product	Interface for discrete signals
Product or Component Type	Slim electromechanical output interface module
Contacts type and composition	1 NO
[Uc] control circuit voltage	24 V
Control circuit type	DC
Width pitch dimension	0.47 in (12 mm)
Maximum [In] rated current	18 mA
Reverse polarity protection	With
Short-circuit protection	6.3 A external fuse fast blow I _k ≤ 1 kA AC and I _k ≤ 100 A DC)
[I _{th}] conventional free air thermal current	5 A IEC 60947-1
Sale per indivisible quantity	5

Complementary

Control circuit voltage limits	28.8 V 14.5 V
Connections - Terminals	Screw clamp terminal
Drop-out voltage	2 V
Holding Current	1.3 mA
Power dissipation in W	0.43 W
Maximum switching voltage	150 V DC 250 V AC
[U _e] rated operational voltage	≤ 120 V DC IEC 60947-5-1 ≤ 230 V AC IEC 60947-5-1
Network Frequency	50/60 Hz
[I _e] rated operational current	1 A AC-14 U _e : 230 V 1000000 cycles IEC 60947-5-1 1 A AC-15 U _e : 230 V 1000000 cycles IEC 60947-5-1 3 A AC-12 U _e : 230 V 1000000 cycles IEC 60947-5-1 1.5 A DC-13 U _e : 24 V 1000000 cycles IEC 60947-5-1 1.7 A DC-12 U _e : 24 V 1000000 cycles IEC 60947-5-1
Minimum switching current	5 mA
Minimum switching voltage	5 V
Electrical reliability	≤ 0.00000001
Operating time	≤ 10 ms between energisation of coil and closing of NO contact DC ≤ 5 ms between de-energisation of coil and closing of NO contact DC
Contact bounce time	≤ 5 ms
Operating rate in Hz	10 Hz at no-load 0.5 Hz at I _e
Mechanical durability	10000000 cycles
[U _i] rated insulation voltage	250 V VDE 0110 group C 300 V IEC 60947-1
Flame retardance	V0 conforming to UL 94
Cable cross section	0.00...0.00 In ² (0.34...2.5 mm ²), 1 or 2 wires flexible with cable end 0.00...0.00 In ² (0.6...2.5 mm ²), 1 or 2 wires flexible without cable end 0.00...0.01 in ² (0.27...4 mm ²), 1 wire rigid
Operating position	Any position

Installation category	II IEC 60947-1
Mounting Support	Symmetrical DIN rail Asymmetrical DIN rail Combination rail
Net Weight	0.09 lb(US) (0.04 kg)

Environment

Immunity to microbreaks	5 ms
Dielectric strength	1000 V for 1 minute between open contacts 2500 V for 1 minute between wired interface and earth 4000 V for 1 minute between coil circuit and contact circuits
Standards	IEC 60947-5-1
Product Certifications	BV CSA DNV LROS (Lloyds register of shipping) UL
IP degree of protection	IP20 conforming to IEC 60529
Protective treatment	TC
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Shock resistance	30 gn 11 ms IEC 60068-2-27
Vibration resistance	3 gn 10...150 Hz)IEC 60068-2-6
Electromagnetic compatibility	Electromagnetic field immunity test level 3 10 V/m between 27...1000 MHz IEC 61000-4-3 Electrostatic discharge immunity test level 3 8 kV IEC 61000-4-2 Fast transients immunity test level 3 on input/output 1 kV IEC 61000-4-4 Fast transients immunity test level 3 on power supply 2 kV IEC 61000-4-4 1.2/50 µs shock waves immunity test IEC 60947-1
Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C) at Us -13...158 °F (-25...70 °C) at Us with 8 mm space between ABR2S1... 23...104 °F (-5...40 °C) unrestricted operation 23...131 °F (-5...55 °C) from 0.85...1.1 Us
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)
Operating altitude	<= 9842.52 ft (3000 m)
Pollution degree	2 IEC 60947-1

Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	3389110651485
Nbr. of units in pkg.	1
Package weight(Lbs)	1.66 oz (47 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.76 in (7 cm)
Package 1 width	3.54 in (9 cm)
Package 1 Length	4.61 in (11.7 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	8.36 oz (237 g)
Package 2 Height	2.76 in (7 cm)
Package 2 width	3.54 in (9 cm)
Package 2 Length	4.61 in (11.7 cm)
Unit Type of Package 3	S02
Number of Units in Package 3	75
Package 3 Weight	8.70 lb(US) (3.946 kg)
Package 3 Height	5.91 in (15 cm)

Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability


Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Slim Electromechanical Interface Module


Dimensions



Slim Electromechanical Interface Module

Example of Application with PLC

Interfacing PLC discrete outputs




- (1) Essential on inductive loads (can be replaced with peak limiter)
- (2) PLC positive logic transistor (or relay) outputs
- (3) PLC analog inputs
- (4) Channel X
- (5) Analog sensors

Slim Electromechanical Interface Module

Circuit Diagram

1 N/O




Electrical Durability of Contacts

AC Loads

Test conditions: in accordance with standard IEC 947-5-1 set up for rated control voltage.


AC-12 operating cycles in millions



AC-12 Control of resistive loads and isolated solid state loads via optocoupler ($\cos \phi \geq 0.9$)

- (1) 24 V
- (2) 48 V
- (3) 115 V
- (4) 230 V

AC-14 and AC-15 operating cycles in millions



AC-14 Control of weak electro-magnetic loads of electro-magnets ≤ 72 VA (make: $\cos \phi = 0.3$, break: $\cos \phi = 0.3$)


AC-15 Control of electro-magnetic loads of electro-magnets > 72 VA (make: $\cos \phi = 0.7$, break: $\cos \phi = 0.4$)

- (1) 24 V
- (2) 48 V
- (3) 115 V
- (4) 230 V

DC Loads

Test conditions: in accordance with standard IEC 947-5-1 set up for rated control voltage.


DC-12 operating cycles in millions



DC-12 Control of resistive loads and isolated solid state loads via optocoupler ($L/R \leq 1$ ms)

- (1) 24 V
- (2) 48 V
- (3) 115 V

DC-13 operating cycles in millions



DC-13 Control of electro-magnets ($L/R \leq 2 \times (U_e \times I_e)$ in ms, with U_e : rated operating voltage and I_e : rated operating current, with a load protection diode

- (1) 24 V
- (2) 48 V
- (3) 115 V

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ABR2S102B](#)