

Product data sheet

Characteristics

LA1LC072F

TeSys Integral - undervoltage trip - 110 V AC
50 Hz - without time delay

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	TeSys
Device short name	LA1LC
Product or component type	Undervoltage trip
Product compatibility	LD4 LD5
Range compatibility	TeSys Integral contactor breaker

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 110...120 V AC 60 Hz
Time delay	Without time delay
Voltage release type	Undervoltage release Instantaneous
Control circuit voltage limits	0.8...1.1 Uc
Threshold tripping voltage	0.35...0.7 Uc
Inrush power in VA	8 VA AC
Hold-in power consumption in VA	4 VA AC
Quantity per set	Set of 10
Product weight	0.33 lb(US) (0.15 kg)

Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901223764
Nbr. of units in pkg.	1
Package weight(Lbs)	0.34000000000000002
Returnability	N
Country of origin	CZ

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Styrene, which is known to the State of California to cause cancer.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LA1LC072F](#)