



Main

Range	TeSys
Device short name	LB1LD
Product or component type	Protection module
Range compatibility	TeSys Integral contactor breaker
Poles description	3P
Utilisation category	AC-43
System Voltage	690 V AC
Thermal protection adjustment range	13...18 A
Magnetic tripping current	108...216 A
Trip unit technology	Thermal-magnetic
Protection type	Phase imbalance
Thermal overload class	Class 20

Complementary

Motor power kW	11 kW at 480...525 V AC 50/60 Hz 15 kW at 600...690 V AC 50/60 Hz 4 kW at 220...240 V AC 50/60 Hz 9 kW at 400...415 V AC 50/60 Hz 9 kW at 440 V AC 50/60 Hz
Product weight	1.72 lb(US) (0.78 kg)



Environment

Standards	NF C 63-650
Protective treatment	TH
IP degree of protection	IP20 B conforming to IEC 60144 IP20 B conforming to IEC 60529
Ambient air temperature for operation	-4...140 °F (-20...60 °C)

Ordering and shipping details

Category	22384 - STARTERS,INTEGRAL,ACCESS
Discount Schedule	I11
GTIN	00785901444954
Nbr. of units in pkg.	1
Package weight(Lbs)	2.3900000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0841 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available  Product Environmental Profile
Product end of life instructions	Available

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LB1LD03M21](#)