

Complementary

Line Rated Current	160 A
AWG gauge	AWG 4...AWG 2/0
Depth	13.09 in (332.49 mm)
Electrical Connection	Screw clamp terminal
Height	13 in (330.20 mm)
Permissible voltage	600 V AC
Net Weight	68 lb(US) (30.84 kg)
Protection Type	Harmonic distortion Current protection Overvoltage protection
Width	13.22 in (335.79 mm)

Environment

Product certifications	UL listed file E180243 CSA LR29753 CE
------------------------	---

Ordering and shipping details

Category	22062-LINE REACTORS/FILTERS (RL,KLC)
Discount Schedule	CP4C
GTIN	785901143826
Nbr. of units in pkg.	1
Package weight(Lbs)	60.00 lb(US) (27.216 kg)
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	12.99 in (33 cm)
Package 1 width	13.23 in (33.6 cm)
Package 1 Length	13.07 in (33.2 cm)

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RL16012](#)