

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

| | |
|---------------------------|---|
| Range of product | Magelis iPC |
| Product or component type | Modular box PC |
| Device short name | Modular BOX PC Performance |
| Processor name | Intel Core i7 4650U 1.7 GHz turbo boost at 3.3 GHz |
| Chipset type | Intel QM87 |
| Free slots | 1 CFast 1 mSATA 2 Internal SATA HDD/SSD with slide-in HMIYMADS-DD1 to mount . hot swap RAID with Intel Rapid Storage Technology |
| Video controller type | Intel HD Graphics 5000 |
| Operating system | Windows 10 IoT Enterprise 64 bit (switched from Windows 8.1 in Q1 2018) multi-language |
| Software package | EcoStruxure secure connect advisor annual subscription cyber security license not included EcoStruxure operator terminal expert run time HMI license not included EcoStruxure machine SCADA expert run time HMI/SCADA on configured offer only EcoStruxure augmented operator advisor server augmented operator license not included Node-RED and system nodes restore IIoT Wiring Operating System Restore McAfee white listing Installer cyber security license not included |

Complementary

| | |
|---------------------------------------|---|
| Range compatibility | Modular Display HMIDM IDisplay |
| Accessory / separate part destination | PC panel on HMIDM modular display |
| Mounting location | Flat mounting Book mounting Wall mounting |
| Data storage equipment | 128 GB Flash disk SSD TLC 1500000 h |
| Memory description | Internal 512 kB MRAM Internal 8 GB RAM DDR3 not expandable |
| Number of slots | 1 PCI 1 PCI express 4x 2 mini PCI Express full-size |
| Display resolution | 3200 x 2000 pixels at 60 Hz |
| Watchdog timer | 1...255 ms |
| Type of cooling | Fanless Fan required to mount PCI/PCIe cards above 3 W |
| Electrical connection | Screw connector pin 1 way ground on bottom Connector SMA 3 ways on top |
| Integrated connection type | Display port with 1 on bottom Display port with 1 on front COM1 serial link battery backup with 1 male SUB-D 9 RS232/422/485 on bottom USB 2.0 port with 2 USB type A, transmission rate: 480 Mbit/s on bottom USB 3.0 port with 2 USB type A, transmission rate: 5 Gbit/s on bottom Ethernet with 2 RJ45 I210, supporting IEEE1588, transmission rate: 10/100/1000 Mbps on bottom TPM connector Ver 1.2 cyber security - hardware encryption TPM module HMIYMINATPM201 to be installed/default installed on mother board |
| [Us] rated supply voltage | 100...240 V AC power supply with additional adaptor HMIYMMAC1 24 V DC power supply |

| | |
|---|--|
| Supply voltage limits | 18...36 V |
| Inrush current | 8.9 A |
| Power consumption in W | 40 W box 44 W with 4:3 12" Display HMIDM6421 43 W with Wide 12" Display HMIDM6521 45 W with 4:3 15" Display HMIDM7421 46 W with Wide 15" Display HMIDM7521 48 W with Wide 19" Display HMIDM9521 51 W with Wide 22" Display HMIDMA521 |
| Control type | ON/OFF button |
| Depth | 4.06 in (103.2 mm) |
| Height | 8.15 in (207 mm) |
| Width | 10 in (254 mm) |
| Product weight | 8.6 lb(US) (3.9 kg) |
| Main type | Performance |
| Number of slots available for expansion | 1 PCI 1 PCI express 4x 2 mini PCIe |

Environment

| | |
|---------------------------------------|---|
| Standards | EN 61131-2 EN 55011 class A group 1 EN 61000-6-4 FCC Part 15 UL 61010 |
| Product certifications | CCC EAC ATEX RCM Marine GL Bridge IEC Ex hazardous locations 3GD zone 2/22 CULus CE CULus CSA 22-2 No 142 CULus HazLoc Class I Division 2 ANSI/ISA 12-12-01 CULus HazLoc Class I Division 2 CSA 22-2 No 213 |
| Quality labels | CE |
| Directives | 2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive |
| IP degree of protection | IP40 conforming to IEC 60529 |
| Electromagnetic compatibility | Conducted and radiated emissions class A EN 55022 Immunity to high frequency interference IEC 61000-4 Disturbing field emission class A EN 55011 |
| Ambient air temperature for storage | -22...158 °F (-30...70 °C) conforming to IEC 60068-2-2 -22...158 °F (-30...70 °C) conforming to IEC 60068-2-14 |
| Relative humidity | 10...95 % non-condensing conforming to EN/IEC 60068-2-30 |
| Ambient air temperature for operation | 32...131 °F (0...55 °C) (by default) conforming to EN/IEC 60068-2-2 32...122 °F (0...50 °C) flat mounting 32...113 °F (0...45 °C) on PCI/PCle HMIDM modular display with HDD 32...104 °F (0...40 °C) flat mounting on HDD 32...104 °F (0...40 °C) flat mounting on mini PCIe 32...104 °F (0...40 °C) flat mounting on PCI/PCle 32...113 °F (0...45 °C) conforming to 2 on mini PCIe HMIDM modular display |
| Operating altitude | 6561.68 ft (2000 m) conforming to IEC 60664-1 |
| Vibration resistance | 1 gn 5...500 Hz HDD 2 gn 5...500 Hz SSD or CFast |


Ordering and shipping details

| | |
|-----------------------|---------------------|
| Category | 22575 - MAGELIS MC3 |
| Discount Schedule | MC3 |
| GTIN | 00785901662501 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 13.200000000000001 |
| Returnability | N |
| Country of origin | US |

Offer Sustainability


| | |
|----------------------------|--|
| RoHS (date code: YYWW) | Compliant - since 1604 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| California proposition 65 | WARNING: This product can expose you to chemicals including: |
| - - - - - Substance 1 | Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. |
| - - - - - More information | For more information go to www.p65warnings.ca.gov |

Dimensions



- (1) Rear view
(2) Left view

Spacing Requirements



- 1 : Air out
- 2 : Air in
- (1) Book mounting : Vertical mounting with rear fixing
- (2) Wall mounting : Vertical mounting with side fixing
- (3) Horizontal mounting

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[HMIBMPSI74D4801](#)