

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	TeSys
Device short name	GS1AM
Product or component type	Auxiliary contact
Contact application	O, I and test position signalling
Contacts type and composition	1 NO
Contact operation	Early-break
[I _{th}] conventional free air thermal current	16 A at 104 °F (40 °C)
[I _e] rated operational current	3 A at 240 V AC-15 6 A at 120 V AC-15 1.5 A at 480 V AC-15 1.8 A at 400 V AC-15 2.8 A at 24 V DC-13 0.15 A at 400 V DC-13 0.27 A at 250 V DC-13 0.55 A at 125 V DC-13 1.4 A at 48 V DC-13

Complementary

Range compatibility	TeSys ,TeSys GS ,GS1 DD ,fuse-switch disconnecter
Mechanical durability	5000000 cycles
Electrical durability	1000000 cycles on AC-15
Product compatibility	GS1
Line Rated Current	600 A 200 A 315 A 1250 A 160 A 63 A 630 A 100 A 400 A 250 A 125 A 50 A 800 A 60 A 32 A
Fuse type	BS NFC DIN
Type of operating handle	External left side External right side External frontal
Product weight	0.03 lb(US) (0.015 kg)

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901367741
Nbr. of units in pkg.	1
Package weight(Lbs)	2.999999999999999E-2

Returnability	Y
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GS1AM110](#)