

Product availability: Stock - Normally stocked in distribution facility



Main

Range	TeSys
Product name	TeSys GS
Device short name	GS2QU
Product or component type	Switch-disconnector-fuse
Device application	Protection
Poles description	3P
Protected poles description	3t
Contacts type and composition	3 NO
[I _{th}] conventional free air thermal current	400 A at 104 °F (40 °C)
[I _e] rated operational current	400 A
Fuse type	UL
Fuse size	J
Network type	AC DC
Network frequency	50/60 Hz

Complementary

Type of operating handle	External frontal
Mounting support	Plate
[U _i] rated insulation voltage	800 V
[U _{imp}] rated impulse withstand voltage	8 kV
Rated operational power in W	220 kW at 690 V 220 kW at 400 V 220 kW at 500 V
Short-circuit withstand	36 kA
Mechanical durability	10000 cycles
Electrical durability	6000 cycles
Connections - terminals	Power circuit: lugs-ring terminals cable 13.3...304 mm ²
Tightening torque	Power circuit: 56.5 N.m

Environment

Standards	UL98 CSA C22.2 No 4
IP degree of protection	IP20 with terminal cover conforming to IEC 60529
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)
Height	9.45 in (240 mm)
Width	10.2 in (259 mm)
Depth	7.09 in (180 mm)

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901549314
Nbr. of units in pkg.	1
Package weight(Lbs)	15.1
Returnability	Y
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0844 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
California proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GS2QU3N](#)