

GV7RS25

TeSys GV7 Manual Starter and Protector,
thermal magnetic circuit protector, rocker lever,
3 P, AC-3, 15...25 A, high interrupt



Main

Range	TeSys
Product name	TeSys GV7
Product or Component Type	Circuit breaker
Device short name	GV7R
Device application	Motor
Poles description	3P
Network type	AC
Utilisation category	AC-3 IEC 60947-4-1
Network frequency	50/60 Hz IEC 60947-4-1
Breaking capacity	50 KA Icu 500 V AC 50/60 Hz IEC 60947-2 65 KA Icu 440 V AC 50/60 Hz IEC 60947-2 100 KA Icu 220/240 V AC 50/60 Hz IEC 60947-2 70 KA Icu 380/415 V AC 50/60 Hz IEC 60947-2 10 kA Icu 660/690 V AC 50/60 Hz IEC 60947-2
[Ics] rated service short-circuit breaking capacity	100 % 440 V AC 50/60 Hz IEC 60947-2 100 % 500 V AC 50/60 Hz IEC 60947-2 100 % 220/240 V AC 50/60 Hz IEC 60947-2 100 % 380/415 V AC 50/60 Hz IEC 60947-2 100 % 660/690 V AC 50/60 Hz IEC 60947-2
Thermal protection adjustment range	15...25 A
Trip unit technology	Thermal-magnetic

Complementary

Mounting Mode	By clips By screws
Mounting Support	Flush Rail Kit for fixing the switchgear Panel mounting
Mounting position	Vertical
Motor power kW	11 KW 500 V AC 50/60 Hz 15 KW 660/690 V AC 50/60 Hz 9 KW 400/415 V AC 50/60 Hz 11 KW 400/415 V AC 50/60 Hz 15 KW 500 V AC 50/60 Hz 18.5 kW 660/690 V AC 50/60 Hz
Control type	Rocker lever
[Ue] rated operational voltage	690 V AC 50/60 Hz IEC 60947-2
[Ui] rated insulation voltage	750 V AC 50/60 Hz IEC 60947-2
[Ith] conventional free air thermal current	25 A IEC 60947-4-1
[Uimp] rated impulse withstand voltage	8 kV IEC 60947-2
Power dissipation per pole	5 W
Power dissipation per pole	5 W
Mechanical durability	50000 cycles
Electrical durability	30000 Cycles AC-3 440 V In 50000 cycles AC-3 440 V In/2
Maximum operating rate	25 cyc/h
Rated duty	Continuous IEC 60947-4-1
Connection pitch	1.38 in (35 mm) without spreaders 1.77 in (45 mm) with spreaders

Connections - terminals	Bars Cable with lug 0.39 in (10 mm) Screw Bare cable connectors 0.00...0.15 in ² (1.5...95 mm ²)
Tightening torque	88.51 Lbf.in (10 N.m) screw M6 132.76 lbf.in (15 N.m) bare cable connectors 0.00...0.15 in ² (1.5...95 mm ²)
Mechanical robustness	Shocks 15 Gn for 11 ms IEC 60068-2-27 Vibrations 2.5 Gn, 0...25 Hz IEC 60068-2-6
Suitability for isolation	Yes IEC 60947-1
Phase failure sensitivity	Yes IEC 60947-4-1 § 7-2-1-5-2
Height	6.34 in (161 mm)
Width	4.13 in (105 mm)
Depth	4.37 in (111 mm)
Net Weight	4.43 lb(US) (2.01 kg)

Environment

Standards	EN/IEC 60947-4-1 NF C 79-130 NF C 63-120 EN/IEC 60947-1 VDE 0113 EN/IEC 60947-2 VDE 0660 NF C 63-650
Product certifications	DNV UL
Protective treatment	TC
IP degree of protection	IP405 IEC 60529 with terminal shrouds)
Pollution degree	3
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-67...203 °F (-55...95 °C)
Fire resistance	1760 °F (960 °C) IEC 60695-2-1
Operating altitude	6561.68 ft (2000 m)

Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	3389110957372
Nbr. of units in pkg.	1
Package weight(Lbs)	4.33 lb(US) (1.963 kg)
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.33 in (11 cm)
Package 1 width	5.91 in (15 cm)
Package 1 Length	6.69 in (17 cm)

Offer Sustainability


EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------


GV7R

Dimensions



(1) 126 for GV7R.220.


Minimum Electrical Clearance




		x1	x2
Painted or insulated metal plate, insulation or insulated bar		0	30
Bare metal plate	U ≤ 440 V	5	35
440 V < U < 600 V		35	
U ≥ 600 V		35	

GV7R


Panel Mounting




Mounting on 2 Mounting Rails DZ5 MB201




Flush-Mounting




1 circuit breaker GV7R




n circuit breakers GV7R side by side



Connection




Smooth terminals




	a
GV7R.40...R.150	19.5
GV7R.220	21.5

Connectors



Motor Circuit Breakers

GV7 R



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV7RS25](#)