

Product data sheet

Characteristics

LK4AD10N

TeSys GS - auxiliary contact 100...400A - 1
NO - 1 NC



Main

Range	TeSys
Product or Component Type	Auxiliary contact
Device Application	Connection
Contacts type and composition	1 NO + 1 NC

Complementary

Range compatibility	TeSys GS switch
Contact operation	Early-break
[I _{th}] conventional free air thermal current	16 A 104 °F (40 °C)
[I _e] rated operational current	100 A 200 A 400 A
Mechanical durability	5000000 cycles
Type of operating handle	External frontal External left side External right side

Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901327417
Nbr. of units in pkg.	1
Package weight(Lbs)	0.71 oz (20 g)
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.39 in (1 cm)
Package 1 width	0.98 in (2.5 cm)
Package 1 Length	1.97 in (5 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[LK4AD10N](#)