


ZCKD019

limit switch head ZCKD - metal end plunger with boot

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKD
Head type	Plunger head
Product compatibility	XCKS
Associated body	ZCKSD39 ZCKSD35 ZCKSD31 ZCKS8 ZCKS1 ZCKS5H29 ZCKS7H29 ZCKSD35H29 ZCKS6H29 ZCKS9 ZCKS9H29 ZCKSD31H29 ZCKSD37 ZCKS8H29 ZCKSD37H29 ZCKS7 ZCKS6 ZCKS5 ZCKS2 ZCKS2H29 ZCKS1H29 ZCKSD39H29
Movement of operating head	Linear
Type of operator	End plunger spring return metal (with protective boot)
Type of approach	Vertical approach 1 direction

Complementary

Switch actuation	On end
Positive opening	With
Head material	Plastic

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22416 - LIMIT SWITCHES,IEC,XCKL
Discount Schedule	T
GTIN	003389110355512
Nbr. of units in pkg.	1
Package weight(Lbs)	0.1000000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKD019](#)