





SERPAC I150HS


Electronic Enclosures




(2) Hinges for p/n 71020
Aluminum Hinged Panel

(4) Bosses for p/n 71000
Aluminum Panel for Bottom

Aluminum panels for bottom,
hinge, and top are not included.
They are available as options:
Bottom panel p/n 71000
Hinged panel p/n 71020
Main panel p/n 71040




See pdf pages 2-4 for panel dimensions
and panel hardware. See page 5 for flange dimensions



-Material: UV stabilized Polycarbonate
Flammability UL 94 V-2
-Watertight enclosure meets or
exceed Nema 4 and or IP67.

PARTS INCLUDED		
P/N	Qty.	Description
150 HST	1	150 HS Top
150 HSB	1	150 HS Bottom
8150	1	150 O-Ring
1304	2	Hinge Pin
1305	2	350 Flange
1306	4	350 Feet
1307	2	350 Panel Hinge Pin
1308	1	350 Panel Hinge A
1309	1	350 Panel Hinge B
6028	4	SS #10 X 5/8" Pan H/L
6031	2	#10 X 1" Screw
8001	2	O-Ring for Screw
6104	2	#10 Threaded Insert

71000 Bottom Panel Kit for I150HL and I150HS




PARTS INCLUDED		
P/N	Qty.	Description
71000	1	Bottom Aluminum Panel
6029	4	#10 X 3/8" Pan Head Screw, 18-8 SS

ALL DIMENSIONS ARE $\pm .010"$

8/3/16


2009 Wright Ave. La Verne, CA 91750
Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com



8/3/16

Ph. (626) 331-0517 Fx. (626) 331-8584 serpac.com



71040 Main Panel Kit for I150HL and I150HS



PARTS INCLUDED		
P/N	Qty.	Description
71040	1	Main Top Aluminum Panel
6029	4	SS #10 X 3/8" Pan HL Screw

I150 Flange Dimensions

I150HL CASE SHOWN BELOW.
FLANGE IS FOR BOTH I150HL AND I150HS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SERPAC:

I150HS,TGBG I150HS,TCBG