

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

|                                         |                                                                                                                                |
|-----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| Range of product                        | OsiSense XM                                                                                                                    |
| Product or component type               | Electronic pressure sensors                                                                                                    |
| Pressure sensor type                    | Pressure transmitter                                                                                                           |
| Pressure switch type of operation       | Pressure transmitter with 2 switching outputs                                                                                  |
| Device short name                       | XMLR                                                                                                                           |
| Pressure sensor size                    | 580.15 psi (40 bar)<br>580 psi                                                                                                 |
| Maximum permissible accidental pressure | 15 MPa<br>2175.57 psi (150 bar)<br>2175 psi                                                                                    |
| Destruction pressure                    | 15 MPa<br>2175 psi<br>2175.57 psi (150 bar)                                                                                    |
| Controlled fluid                        | Fresh water (32...176 °F (0...80 °C))<br>Air (-20...80 °C)<br>Hydraulic oil (-20...80 °C)<br>Refrigeration fluid (-20...80 °C) |
| Fluid connection type                   | G 1/4 (female) conforming to DIN 3852-Y                                                                                        |
| [Us] rated supply voltage               | 24 V DC SELV, voltage limits: 17...33 V                                                                                        |

### Complementary

|                                                         |                                                                                           |
|---------------------------------------------------------|-------------------------------------------------------------------------------------------|
| Current consumption                                     | <= 50 mA                                                                                  |
| Electrical connection                                   | 5 pins M12 male connector                                                                 |
| Analogue output function                                | 4...20 mA                                                                                 |
| Type of output signal                                   | Analogue + discrete                                                                       |
| Analogue output function                                | 4...20 mA                                                                                 |
| Discrete output type                                    | Solid state NPN, 2 NO/NC programmable                                                     |
| Maximum switching current                               | 250 mA                                                                                    |
| Contacts type and composition                           | 2 NO/NC programmable                                                                      |
| Scale type                                              | Fixed differential                                                                        |
| Voltage drop                                            | <= 2 V                                                                                    |
| Adjustable range of switching point on rising pressure  | 0.32...4 MPa<br>46.41...580.15 psi (3.2...40 bar)<br>46.4...580 psi                       |
| Adjustable range of switching point on falling pressure | 29.01...562.75 psi (2...38.8 bar)<br>29...563 psi<br>0.2...3.88 MPa                       |
| Minimum differential travel                             | 17.4 psi (1.2 bar)<br>17.4 psi<br>120 kPa                                                 |
| Materials in contact with fluid                         | 316L stainless steel<br>Fluorocarbon FKM (Viton)<br>Ceramic                               |
| Front material                                          | Polyester                                                                                 |
| Housing material                                        | 316L stainless steel<br>Polyacrylamide                                                    |
| Operating position                                      | Any position, but disposals can falsified the measurement in case of upside down mounting |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

|                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
|------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protection type                          | Overvoltage protection<br>Overload protection<br>Reverse polarity<br>Short-circuit protection                                                                                                                                                                                                                                                                                                                                                                                                               |
| Response time on output                  | <= 10 ms analog output<br><= 5 ms discrete output                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Switching output time delay              | 0...50 s in steps of 1 second                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Display type                             | 4 digits 7 segments                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Local signalling                         | 2 LEDs yellow light ON when switch is actuated                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Display response time type               | Fast 50 ms<br>Normal 200 ms<br>Slow 600 ms                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Delay first up                           | <= 300 ms                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Overall accuracy                         | <= 1 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Linearity error on analogue output       | <= 0.5 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Hysteresis on analogue output            | <= 0.2 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Measurement accuracy on switching output | <= 0.6 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Repeat accuracy                          | <= 0.2 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Drift of the sensitivity                 | +/- 0.03 % of measuring range/°C                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Drift of the zero point                  | +/- 0.1 % of measuring range/°C                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Display accuracy                         | <= 1 % of the measuring range                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Mechanical durability                    | >= 10000000 cycles                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Depth                                    | 1.65 in (42 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Height                                   | 3.66 in (93 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Width                                    | 1.61 in (41 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Product weight                           | 0.42 lb(US) (0.19 kg)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                       |
| [Uimp] rated impulse withstand voltage   | 0.5 kV DC                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Electromagnetic compatibility            | Electrostatic discharge immunity test - test level 8 kV air, 4 kV contact conforming to EN/IEC 61000-4-2<br>Susceptibility to electromagnetic fields - test level 10 V/m (80...2000 MHz) conforming to EN/IEC 61000-4-3<br>Electrical fast transient/burst immunity test - test level 2 kV conforming to EN/IEC 61000-4-4<br>Surge immunity test - test level 1 kV conforming to EN/IEC 61000-4-5<br>Immunity to conducted RF disturbances - test level 10 V (0.15...80 MHz) conforming to EN/IEC 61000-4-6 |

## Environment

|                                       |                                                                    |
|---------------------------------------|--------------------------------------------------------------------|
| Marking                               | CE                                                                 |
| Product certifications                | EAC<br>cULus                                                       |
| Standards                             | EN/IEC 61326-2-3<br>UL 61010-1                                     |
| Ambient air temperature for operation | -4...176 °F (-20...80 °C)                                          |
| Ambient air temperature for storage   | -40...176 °F (-40...80 °C)                                         |
| IP degree of protection               | IP65 conforming to EN/IEC 60529<br>IP67 conforming to EN/IEC 60529 |
| Vibration resistance                  | 20 gn (f = 10...2000 Hz) conforming to EN/IEC 60068-2-6            |
| Shock resistance                      | 50 gn conforming to EN/IEC 60068-2-27                              |

## Ordering and shipping details

|                       |                                         |
|-----------------------|-----------------------------------------|
| Category              | 21551 - XMLF,XMLF,XMLG PRESSURE SENSORS |
| Discount Schedule     | DS2                                     |
| GTIN                  | 003389119611152                         |
| Nbr. of units in pkg. | 1                                       |
| Package weight(Lbs)   | 0.41999999999999998                     |
| Returnability         | N                                       |
| Country of origin     | CH                                      |

## Offer Sustainability

|                            |                                                                                                                                    |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| RoHS (date code: YYWW)     | Compliant - since 1351 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                      | Reference not containing SVHC above the threshold                                                                                  |
| California proposition 65  | WARNING: This product can expose you to chemicals including:                                                                       |
| - - - - - Substance 1      | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                        |
| - - - - - Substance 2      | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.          |
| - - - - - More information | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                      |

## Dimensions




---

Connections and Schema

---

Connector Wiring



## Analogue Output Description

Analogue Output Signal



X : Pressure

Y : Analogue output signal

(1) An offset of +/-5% of nominal pressure can be compensated (with Cof Configuration menu. Cof: Offset Compensation)

(2) The analogue curve can be adjusted from -25% to +25% of nominal pressure (with AEP Configuration menu. AEP: analogue end point).

## Switching Output Description. Hysteresis Mode

The hysteresis switching mode is typically used for the "pumping and/or emptying applications".



X : Time

Y : Pressure

(1) Output

NP : Nominal Pressure

SP : Set point (adjustable from 8 % to 100 % NP)

rP : Reset point (adjustable from 5 % to 97 % NP)

## Switching Output Description. Window Mode

The window switching mode is typically used for the "pressure regulation applications"



X : Time  
 Y : Pressure  
 (1) : Output  
 NP : Nominal pressure  
 FH : High switching point (adjustable from 8 % to 100 % NP)  
 FL : Low switching point (adjustable from 5 % to 97 % NP)

### Switching Output Description. Time Delay

The Time Delay is typically used to filter out the fast pressure transients.  
 The output only switches after a time "dS" and "dr" adjustable from 0 to 50 seconds.



X : Time  
 Y : Pressure  
 (1) : Output  
 SP : Set point  
 rP : Reset point  
 dS : Time delay on the set point  
 dr : Time delay on the reset point

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XMLR040G2N25](#)