


### Features

- Ultra Small size of 2" x 3" x 1.0"
- For 1U Applications
- 60W convection cooled
- Universal Input 90-264Vac
- Approved to IEC60601-1, 3<sup>rd</sup> Edition with 2 MOPP
- Level V Efficiency Compliant Models
- Less than 0.5W no-load Power Consumption
- 3 Year Warranty
- Optional LED indicator for power-on
- RoHS Compliant

 **RoHS**



**CE**

### Description

The MB60S Series models provide a reliable power source in high power density in 2" x 3" x 1.0" package. Fully compliant to the applicable safety and EMC standards, these models will allow easy integration into many Medical applications. All 6 models are CE marked to low voltage directive and approved to Medical standards of IEC60601-1 3<sup>rd</sup> edition with 2 MOPP.

### Model Selection

| Model Number | Volts | Output Current<br>Convection Cooled | Output Power<br>Convection Cooled | Ripple & Noise* | Total Regulation | OVP Threshold |
|--------------|-------|-------------------------------------|-----------------------------------|-----------------|------------------|---------------|
| MB60S12K     | 12V   | 4.58A                               | 55W                               | 120mV pk-pk     | ±2%              | 14.4-18Vdc    |
| MB60S15K     | 15V   | 4.00A                               | 60W                               | 150mV pk-pk     | ±2%              | 18-22.5Vdc    |
| MB60S18K     | 18V   | 3.33A                               | 60W                               | 180mV pk-pk     | □2%              | 21-25.5Vdc    |
| MB60S24K     | 24V   | 2.50A                               | 60W                               | 240mV pk-pk     | ±2%              | 28.8-36Vdc    |
| MB60S36K**   | 36V   | 1.67A                               | 60W                               | 360mV pk-pk     | ±2%              | 42-47Vdc      |
| MB60S48K     | 48V   | 1.25A                               | 60W                               | 480mV pk-pk     | ±2%              | 57.6-72Vdc    |

Notes:

\* At -20C, the noise and ripple is 2% of the output.

\*\* For product availability, please contact the factory

### Input Specifications

| PARAMETER                      | SPECIFICATION               | NOTES        |
|--------------------------------|-----------------------------|--------------|
| <b>AC Input Voltage:</b>       | 90-264Vac, single phase     |              |
| <b>AC Input Frequency:</b>     | 47-63Hz                     |              |
| <b>AC Input Current:</b>       | 120Vac: 1.4A, 240Vac: 0.75A |              |
| <b>Turn-on Input Voltage:</b>  | 70V                         | Ramping Up   |
| <b>Turn-off Input Voltage:</b> | 65V                         | Ramping Down |
| <b>Inrush Current:</b>         | 40A maximum @ 0C            |              |

|  |   |   |
|--|---|---|
| <b>Leakage Current (Input–Earth):</b>  | <275 $\mu$ A@264Vac, 60 Hz input, NC                      | IEC 60601-1 3 <sup>rd</sup> Ed – 8.7.3.c          |
| <b>Leakage Current (Output–Earth):</b> | N/A   |   |
| <b>Leakage Current (Input-Output):</b> | <90 $\mu$ A@264Vac, 60 Hz input, NC                       |   |
| <b>Input Fuses:</b>                    | F1, F2: 4A, 250VAC  | Fuses provided on all models                      |
| <b>Efficiency</b>                      | Typical   | Measured at 120Vac and full load                  |
| MB60S12K                               | 83%   |   |
| MB60S15K                               | 85%   |   |
| MB60S18K                               | 85%   |   |
| MB60S24K                               | 88%   | 24V, 36V, and 48V Models meet Level V requirement |
| MB60S36K                               | 88%   |   |
| MB60S48K                               | 88%   |   |
| <b>No Load Input Power:</b>            | <0.5W   | Meet Level V, standby Power Consumption           |
| <b>Turn-on Time:</b>                   | <2 Seconds at 120Vac.                                     |   |
| <b>Hold-up Time:</b>                   | 16mS minimum from loss of ac input at 120 Vac, full load. | 55 Watts for 12V output                           |

### DC Output Specifications

| PARAMETER                          | SPECIFICATION  | NOTES   |
|------------------------------------|--|---|
| <b>Output Power:</b>               | 60W continuous for operation from -10°C to 50°C<br>55 Watts for 12V output.  |   |
| <b>Cooling:</b>                    | Convection   |   |
| <b>Total Regulation:</b>           | $\pm 2\%$ for all models   | Total regulation is the maximum deviation from nominal voltage for all loading conditions   |
| <b>Overload Protection:</b>        | 120% - 180% of rated output current value, Hiccup Mode   |   |
| <b>Short Circuit Protection:</b>   | Short across the output terminals will not cause damage to the unit. Hiccup Mode   |   |
| <b>Overvoltage Protection:</b>     | OVP firing reduces output voltage to <50% of nominal in <50mS. See chart for trip range  |   |
| <b>Overtemperature Protection:</b> | Automatic Power Shutdown at $T_c = 155^\circ\text{C}$ ,  |   |
| <b>Minimum Load:</b>               | No minimum load is required  |   |
| <b>Ripple and Noise:</b>           | 0.5% RMS, 1% pk-pk for all models.   | 20 MHz Bandwidth, differential mode. Measured with noise probe directly across output terminals, and load terminated with 0.1 $\mu$ F ceramic and 10 $\mu$ F low ESR capacitors |
| <b>Transient Response:</b>         | 500 $\mu$ s typ. response time for return to within 0.5% of final value for a 50% load change, $\Delta i/\Delta t < 0.2\text{A}/\mu\text{s}$ . Max. voltage deviation is 3.5%. |   |
| <b>Overshoot:</b>                  | 5% overshoot at turn-on, 5% overshoot at turn-off, under all conditions.   |   |

### Safety Standard Compliance

| Agency          | CONDITIONS                                      |
|-----------------|---|
| UL              | ANSI/AAMI ES60101:2005, 3 <sup>rd</sup> Edition |
| CSA             | CAN/CSA-C22.2 No. 60601-1 (2008)                |
| Demko           | EN 60601-1:2006                                 |
| CB Report       | IEC 60601-1 (3 <sup>rd</sup> Edition)           |
| Isolation Type: | B rated   |

### Isolation Specifications

| PARAMETER                       | CONDITIONS       | Rating  | NOTES |
|---------------------------------|------------------|---------|-------|
| Insulation Safety Rating:       | Input to Ground  | 2 MOPP  |       |
|                                 | Input to Output  | 1 MOPP  |       |
|                                 | Output to Ground | 1 MOPP  |       |
| Electric Strength Test Voltage: | Input to Ground  | 1800Vac |       |
|                                 | Input to Output  | 4000Vac |       |
|                                 | Output to Ground | 500Vac  |       |

### Environmental Specifications

| PARAMETER              | SPECIFICATION   | NOTES  |
|------------------------|---|--|
| Operating Temperature: | -10°C to +80°C  | -40°C Startup guaranteed                                   |
| Temperature Derating:  | For 24V output and over, derate output power to 50W @ 60C, 40 Watt @ 70C, and 20 Watts for 80C      | <24V will derate to 40W at 60C, 30W at 70C, and 20W at 80C |
| Cooling:               | Convection  |  |
| Storage Temperature:   | -40°C to +85°C  |  |
| Altitude:              | Operating: -500 to 3,000 meter<br>Non-operating: -500 to 40,000 ft.                                 |  |
| Relative Humidity:     | 5% to 95%, non-condensing   |  |
| Shock:                 | Non-Operating: Half-sine, 40 gpk, 10mS, 3 axes, 6 shocks total                                      |  |
| Vibration:             | Random vibration per MIL-STD-810E, Method 514.4, Cat. 1, Figure 514.4-1, 1 hr in each of three axes |  |

### Reliability Specifications

| PARAMETER  | SPECIFICATION                          | NOTES   |
|------------|--|---|
| MTBF:      | 700,000 hours, 25°C ambient, full load | Calculation is done based on Telcordia. Reports for each model is available |
| Warranty:  | 3 Years                                | Limited   |
| HALT Data: | Per SL Power Halt procedure            | Report is available   |


### EMI/EMC Compliance

| PARAMETER                                  | SPECIFICATION  | NOTES   |
|--|--|---|
| <b>Conducted Emissions:</b>                | EN55011/22 Class B; FCC Part 15  |   |
| <b>Radiated Emissions:</b>                 | EN55011/22 Class A; FCC Part 15  |   |
| <b>Harmonic Current Emissions</b>          | EN61000-3-2, Class A   |   |
| <b>Voltage Fluctuations &amp; Flicker</b>  | EN61000-3-3  |   |
| <b>Static Discharge Immunity:</b>          | EN61000-4-2, Level 4: 6kV contact, 8kV air, Criteria A   | Performance criteria are defined as following:<br><br>A – Normal performance during and after the test<br>B – Temporary degradation, self-recoverable<br>C – Temporary degradation, operator intervention required to recover the operation |
| <b>RF Field Susceptability</b>             | EN61000-4-3, Level 3 (3V/m), Criteria A  |   |
| <b>Fast Transients/Bursts</b>              | EN61000-4-4, Level 3 (PS: 2kV-40A, other lines 1kV-20A), Criteria B  |   |
| <b>Surge Susceptability</b>                | EN61000-4-5, Installation Class 3 (1kV diff. mode, 2kV common mode), Criteria A                            |   |
| <b>Conducted RF Susceptability</b>         | EN61000-4-6, Level 3 (3Vrms), Criteria A   |   |
| <b>Power Frequency Magnetic Field Test</b> | EN61000-4-8, Level 3 (3A/m), Criteria A  |   |
| <b>Voltage Sags &amp; Surges</b>           | EN61000-4-11,<br>95% dip/0.5 cycle (Criteria A),<br>60%/5cycles (Criteria B ), 30%/25 cycles (Criteria A). |   |

### Notes:

1. Specifications subject to change without notice.
2. Specifications are for convection rating at factory settings with 115Vac input and 25°C ambient unless otherwise stated.

## Mechanical Drawing



## Connector Information

| Input Connector<br>J100                                   | DC Output<br>Connector<br>J2                                 | Ground<br>(FG)   |
|---|--|--|
| PIN 1) AC LINE<br>PIN 2) EMPTY<br>PIN 3) AC NEUTRAL       | PIN 1) +Vout<br>PIN 3) -Vout<br>PIN 2) +Vout<br>PIN 4) -Vout | 19-30258-0187 (Keystone 1285)<br>(Zierick 895)(.187*0.020) |
| Mating Connector:<br>Tyco/AMP 640250-3<br>Pins = 770461-1 | Mating Connector:<br>AMP 640250-4<br>Pins = 770461-1         | Mating Connector<br>Molex 19002-0005                       |

1. Mounting holes should be connected together for EMI purpose
2. FG is safety ground connection
3. This power supply requires mounting on metal standoffs 0.20" (5mm) in height

## Characteristic Curves

### Output vs. Temperature

-40°C start up. At -20°C, the supply meet its full spec except ripple & noise might be increased from 1% to 2% of the output voltage

55W convection cooled, derating output power to 30W at 70°C for outputs 12V and 15V

60W convection cooled, derating output power to 50W at 60°C and 40W at 70°C for Output Voltages  $\geq 24V$

20W convection cooled at 80°C




Fig.1

### Efficiency vs. Loading






Fig.2


To verify that the output ripple and noise does not exceed the level specified in the product specification, measured using a scope probe socket with 0.1uF ceramic and a 10uF electrolytic capacitor connected in parallel across it, 20MHz BW.




[24V OUT, FULL LOAD, 90VAC, 60Hz](#)



[24V OUT, No Load, 90VAC, 60Hz](#)



[24V OUT, No Load, 264VAC, 50Hz](#)




[24V OUT, FULL LOAD, 264VAC, 50Hz](#)




### Output Transient Response

50% load step within the regulation limits of minimum and maximum load,  $di/dt < 0.2A/\mu\text{Sec}$ . Recovery time not specified as there is no laps in regulation with a 50% Load Step. Maximum voltage deviation is 3.5%




[24V OUT, 120VAC, 25% TO 75% LOAD STEP](#)




[24V OUT, 240VAC, 25% TO 75% LOAD STEP](#)

### Output Overload Characteristic




[24V OUT, 90VAC](#)




[24V OUT, 264VAC](#)

### Short Circuit Protection

Supply shall protect itself against Short Circuit conditions. No damage will occur if the output is shorted.



[24V OUT, 264VAC](#)




[24V OUT, 90VAC](#)


### Overvoltage Protection



OVP firing reduces output voltage to <50% of nominal in <50ms. See models chart for trip ranges.




24V OUT, FULL LOAD, 90VAC, 60Hz




24V OUT, FULL LOAD, 264VAC, 50Hz

### Turn On Time




24V OUT, FULL LOAD, 90VAC, 60Hz



24V OUT, FULL LOAD, 264VAC, 50Hz

### Hold Up Time



24V OUT, FULL LOAD, 120VAC, 60Hz

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SL Power:

[MB60S36K](#) [MB60S24K](#) [MB60S18K](#) [MB60S48K](#) [MB60S12K](#) [MB60S15K](#) [MB60S13C](#)