



Keying Shown as example

CHARACTERISTICS


- Standard : Based on MIL-DTL-38999 Series III
- Shell Material : Aluminium
- Shell Plating : Black Zinc Nickel
- Insulator : Thermoplastic
- Contacts : Copper Alloy
- Seals & Grommet : Silicon Elastomer
- Contact Plating : Gold over copper Alloy 0.8µm minimum
- Durability : 500 Mating cycles
- Delivered with Souriau contacts and Accessories
- Temperature Range : -65°C to +175°C
- Salt Spray : 500 hours
- Mass : 101.3 g ± 10%

| Connector dimension | |
|---------------------|-----------------|
| Dim | Nominal |
| A | 58.7±0.3 |
| B | 42.85±0.1/-0.15 |
| R | 32.5Max |
| S | 55.6±0.4 |
| W | 3+0.9/-0.1 |
| VV THREAD | M37x1-6g |


SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| | |
|---------|-----------------------------|
| Country | Jurisdiction & Control List |
| FR | Not Listed |

PN: 8D725Z19BN

| | | | | |
|--------------|---|--------------------------------|------------------|--|
| A | 05-10-2016 | First Release | | |
| ISS | DATE | Latest modification - by | | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING | |
| TITLE | | Aluminium Receptacle 8D series | | |
| SCALE |  | General linear | NPRDS / PROJECT | |
| NA | | Tolerances: ±-- | 859 | |
| SOURIAU | | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D725Z19BN-C | | | SHEET 1/2 |
| A3 | | | | |

Contact Layout




| Contacts (Insert arrangement 25-19) | | | | | |
|--|--------------|--------------|---------------------|-------------|--------------|
| Contact position ID | Location | | Contact position ID | Location | |
| | X-axis (mm) | Y-axis (mm) | | X-axis (mm) | Y-axis (mm) |
| A | +000 (0.00) | +409 (10.39) | L | -354 (8.99) | +205 (5.21) |
| B | +236 (5.99) | +409 (10.39) | M | -236 (5.99) | +409 (10.39) |
| C | +354 (8.99) | +205 (5.21) | N | -118 (3.00) | +205 (5.21) |
| D | +472 (11.99) | +000 (0.00) | P | +118 (3.00) | +205 (5.21) |
| E | +354 (8.99) | -205 (5.21) | R | +236 (5.99) | +000 (0.00) |
| F | +236 (5.99) | -409 (10.39) | S | +118 (3.00) | -205 (5.21) |
| G | +000 (0.00) | -409 (10.39) | T | -118 (3.00) | -205 (5.21) |
| H | -236 (5.99) | -409 (10.39) | U | -236 (5.99) | +000 (0.00) |
| J | -354 (8.99) | -205 (5.21) | V | +000 (0.00) | +000 (0.00) |
| K | -472 (11.99) | +000 (0.00) | --- | --- | --- |

| Shell size | Arrangement no. | Number of contacts | Size contacts | Service rating | Contact location | Supersedes |
|------------|-----------------|--------------------|---------------|----------------|------------------|------------|
| 25 | -19 | 19 | 12 | I | All | MS20057-19 |

Panel cutout

JAM NUT RECEPTACLE (TYPE 7)




| Dim | Nominal |
|-----|---------------|
| B | 43.43+0/-0.25 |
| ØC | 44.7+0.25/-0 |

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

| Country | Jurisdiction & Control List |
|---------|-----------------------------|
| FR | Not Listed |

PN: 8D725Z19BN

| | | | | |
|--------------|---|--------------------------------|------------------|--|
| A | 05-10-2016 | First Release | | |
| ISS | DATE | Latest modification - by | | MOD N° |
| Designed By: | | Date: | CUSTOMER DRAWING | |
| TITLE | | Aluminium Receptacle 8D series | | |
| SCALE |  | General linear Tolerances: | NPRDS / PROJECT | |
| NA | | ±-- | 859 | |
| SOURIAU | | WWW.SOURIAU.COM | | This document is the property of SOURIAU it must not be reproduced or communicated without permission |
| FORMAT | SOURIAU DRG N° 8D725Z19BN-C | | | SHEET 2/2 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[8D725Z19BN](#)