








THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.


THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.


DWG. NO.
JBX2INSFPC

FEMALE INSULATOR, PCB CONTACT

CONTACT LAYOUT	04	05
FRONT SIDE VIEW		
REAR SIDE VIEW		
CONTACT		
ISO VIEW		
CONTACT	ØC	1.3
	ØF	0.7
	MAX. AWG	-
	MAX. CURRENT RATING (A)	15
	CONTACT RESISTANCE (mΩ)	3
INSULATOR	NUMBER OF CAVITY	4
	MAX. CURRENT RATING	15
	TEST VOLTAGE (Vrms)	2400
	WORKING VOLTAGE (Vdc/Vrms)	1000/700

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
			
TOLERANCES			
UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES ±1°			



CONTACT TYPE : F (FEMALE)

CONTACT TERMINATION : P (PCB)

MATERIAL :

CONTACT: CUPRO-NICKEL

INSULATOR: PEEK

FINISH:

CONTACTS : GOLD

CATALOG NUMBER DESCRIPTION

JBXXX 2 XYYFP XXXX

BASIC SERIES

SHELL TYPE

SHELL SIZE

KEYING

CONTACT LAYOUT

OPTION

INSERT MATERIAL

COLLET OPTION

SURFACE PLATING

CONTACT TERMINATION

CONTACT TYPE

B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	TJS 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE				
JBX, SIZE 2, FEMALE INSULATOR, PCB CONTACT				
CAT NO.				
JBX2INSFP				
CAGE NO: 09922	SIZE: B		APPROVAL	
CUSTOMER	SOURIAU	DRAWN: TJS		02-04-15
		CHKD : EV		02-04-15
		DSGN : EV		02-04-15
		MFG : DH		02-04-15
		QC : BB		02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.	WWW.SOURIAU.COM	DRAWING SCALE: NA		
		DRAWING NO.		REV
		JBX2INSFPC	B	
		1 OF 4		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFPC

CONTACT LAYOUT		06	07	08	10
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	1.3	1.3	0.9	0.9
	ØF	0.7	0.7	0.7	0.7
	MAX. AWG	-	-	-	-
	MAX. CURRENT RATING (A)	15	15	10	10
	CONTACT RESISTANCE (mΩ)	3	3	3.5	3.5
	NUMBER OF CAVITY	6	7	8	10
	MAX. CURRENT RATING	12	11	10	8
	TEST VOLTAGE (Vrms)	1900	1500	1700	1700
INSULATOR	WORKING VOLTAGE (Vdc/Vrms)	900/630	730/500	830/560	830/560

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE				
JBX, SIZE 2, FEMALE INSULATOR, PCB CONTACT				
CAT NO.				
JBX2INSFP				
CAGE NO: 09922	SIZE: B		APPROVAL	
CUSTOMER	SOURIAU	DRAWN: TJS		02-04-15
		CHKD : EV		02-04-15
		DSGN : EV		02-04-15
		MFG : DH		02-04-15
		QC : BB		02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		DRAWING SCALE: NA		
		DRAWING NO.		REV
		JBX2INSFPC		B
		2 OF 4		

WWW.SOURIAU.COM

PRO-E

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFPC

CONTACT LAYOUT		12	16	18	19
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	0.7	0.7	0.7	0.7
	ØF	0.5	0.5	0.5	0.5
	MAX. AWG	-	-	-	-
	MAX. CURRENT RATING (A)	7	7	7	7
INSULATOR	CONTACT RESISTANCE (mΩ)	5	5	5	5
	NUMBER OF CAVITY	12	16	18	19
	MAX. CURRENT RATING	7	6	5.5	5
	TEST VOLTAGE (Vrms)	1700	1500	1400	1400
WORKING VOLTAGE (Vdc/Vrms)		830/560	730/500	660/460	660/460

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:

mm

INCH

mm (INCH)

THIRD ANGLE PROJECTION

TOLERANCES UNLESS OTHERWISE SPECIFIED

No. OF PLACES	mm [INCH]
ONE PLACE	±3 [±.1]
TWO PLACES	±0.5 [±.02]
THREE PLACES	±0.25 [±.010]

ANGLES±1°

DRAWING TITLE

JBX, SIZE 2, FEMALE INSULATOR, PCB CONTACT

CAT NO.

JBX2INSFP

CAGE NO: 09922

SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.

SOURIAU

WWW.SOURIAU.COM


APPROVAL

DRAWN:	TJS	02-04-15
CHKD :	EV	02-04-15
DSGN :	EV	02-04-15
MFG :	DH	02-04-15
QC :	BB	02-04-15
DRAWING SCALE: NA		
DRAWING NO.		REV
JBX2INSFPC		B
3 OF 4		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.


THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFPC



1. ALL DIMENSIONS ARE ± 0.05
2. SEE TABLE 1 FOR RECOMMENDED FINISHED PCB HOLE SIZE.

TABLE 1	
CONTACT PCB TAIL SIZE DIA	FINISHED PCB HOLE SIZE DIA
0.5	0.75
0.7	0.95



SAMPLE ASSEMBLY FOR INFORMATION

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99

These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited

LINEAR MEASURE:	
THIRD ANGLE PROJECTION	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	mm [INCH]
ONE PLACE	$\pm 3 [\pm .1]$
TWO PLACES	$\pm 0.5 [\pm .02]$
THREE PLACES	$\pm 0.25 [\pm .010]$
ANGLES $\pm 1^\circ$	

DRAWING TITLE
JBX, SIZE 2, FEMALE INSULATOR, PCB CONTACT

CAT NO.
JBX2INSFP

CAGE NO: 09922SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.

SOURIAU

WWW.SOURIAU.COM

APPROVAL

DRAWN: TJS02-04-15
CHKD : EV02-04-15
DSGN : EV02-04-15
MFG : DH02-04-15
QC : BB02-04-15

DRAWING SCALE: NA
DRAWING NO. REV
JBX2INSFPC B

4 OF 4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXEP2G08FPSDS](#) [JBXEP2G10FPSDS](#) [JBXEP2G16FPSDS](#) [JBXEP2G18FPSDS](#) [JBXEP2G19FPSDS](#)
[JBXEP2G04FPSDS](#) [JBXEP2G12FPSDS](#)