










THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

MALE INSULATOR, CRIMP CONTACT

DWG. NO.
JBX2INSMCC


CONTACT LAYOUT		02	03
FRONT SIDE VIEW			
REAR SIDE VIEW			
CONTACT			
ISO VIEW			
CONTACT	ØC	2	1.6
	ØF	2.4	1.9
	MAX. AWG	12	14
	MAX. CURRENT RATING (A)	30	17
INSULATOR	CONTACT RESISTANCE (mΩ)	2.5	2.5
	NUMBER OF CAVITY	2	3
	MAX. CURRENT RATING	30	17
	TEST VOLTAGE (Vrms)	2100	1700
WORKING VOLTAGE (Vdc/Vrms)		1000/700	830/560



CONTACT TYPE : M (MALE)
CONTACT TERMINATION : C (CRIMP)

MATERIAL :
CONTACT: BRASS
CLIP: COPPER ALLOY
INSULATOR: PEEK
FINISH:
CONTACTS: GOLD

CATALOG NUMBER DESCRIPTION



B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	SKV 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE
JBX, SIZE 2, MALE INSULATOR, CRIMP CONTACT

CAT NO.
JBX2INSMC

CAGE NO: 09922SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.

APPROVAL

DRAWN: SKV 02-02-15
CHKD : EV 02-02-15
DSGN : EV 02-02-15
MFG : DH 02-02-15
QC : BB 02-02-15

DRAWING SCALE: NA
DRAWING NO.
JBX2INSMCC

REV
B

1 OF 3

WWW.SOURIAU.COM

PRO-E

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:

mm

INCH

mm (INCH)

THIRD ANGLE PROJECTION

TOLERANCES UNLESS OTHERWISE SPECIFIED

No. OF PLACES

mm [INCH]

ONE PLACE

±3 [±.1]

TWO PLACES

±0.5 [±.02]

THREE PLACES





















±0.25 [±.010]

ANGLES±1°


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSMCC

CONTACT LAYOUT		04	05	06	07	08	10
FRONT SIDE VIEW							
REAR SIDE VIEW							
CONTACT							
ISO VIEW							
CONTACT	ØC	1.3	1.3	1.3	1.3	0.9	0.9
	ØF	1.4	1.4	1.4	1.4	1.1	1.1
	MAX. AWG	18	18	18	18	20	20
	MAX. CURRENT RATING (A)	15	15	15	15	10	10
	CONTACT RESISTANCE (mΩ)	3	3	3	3	3.5	3.5
INSULATOR	NUMBER OF CAVITY	4	5	6	7	8	10
	MAX. CURRENT RATING	15	14	12	11	10	8
	TEST VOLTAGE (Vrms)	2400	1900	1900	1500	1700	1700
	WORKING VOLTAGE (Vdc/Vrms)	1000/700	900/630	900/630	730/500	830/560	830/560

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES ±1°			

DRAWING TITLE				
JBX, SIZE 2, MALE INSULATOR, CRIMP CONTACT				
CAT NO.				
JBX2INSMC				
CAGE NO: 09922	SIZE: B		APPROVAL	
CUSTOMER	SOURIAU	DRAWN: SKV		02-02-15
		CHKD : EV		02-02-15
		DSGN : EV		02-02-15
		MFG : DH		02-02-15
		QC : BB		02-02-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.	WWW.SOURIAU.COM	DRAWING SCALE: NA		
		DRAWING NO. REV		
		JBX2INSMCC	B	
2 OF 3				

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSMCC

CONTACT LAYOUT		12	16	18	19
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	0.7	0.7	0.7	0.7
	ØF	0.85	0.85	0.85	0.85
	MAX. AWG	22	22	22	22
	MAX. CURRENT RATING (A)	7	7	7	7
INSULATOR	CONTACT RESISTANCE (mΩ)	5	5	5	5
	NUMBER OF CAVITY	12	16	18	19
	MAX. CURRENT RATING	7	6	5.5	5
	TEST VOLTAGE (Vrms)	1700	1500	1400	1400
	WORKING VOLTAGE (Vdc/Vrms)	830/560	730/500	660/460	660/460

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE						
JBX, SIZE 2, MALE INSULATOR, CRIMP CONTACT						
CAT NO.						
JBX2INSMC						
CAGE NO: 09922		SIZE: B		APPROVAL		
CUSTOMER		SOURIAU			DRAWN: SKV	02-02-15
					CHKD : EV	02-02-15
					DSGN : EV	02-02-15
					MFG : DH	02-02-15
					QC : BB	02-02-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM			DRAWING SCALE: NA	
					DRAWING NO. REV	
					JBX2INSMCC B	
					3 OF 3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXFD2G07MCSDSR](#) [JBXFD2G10MCSDSR](#) [JBXFD2G05MCSDSR](#) [JBXFD2G12MCSDSR](#) [JBXFD2G10MCSDSMR](#)
[JBXFD2G16MCSDSMR](#) [JBXFD2G18MCSDSMR](#) [JBXFD2G02MCSDSMR](#) [JBXFD2G02MCSDSR](#)
[JBXFD2G03MCSDSMR](#) [JBXFD2G03MCSDSR](#) [JBXFD2G04MCSDSMR](#) [JBXFD2G04MCSDSR](#)
[JBXFD2G05MCSDSMR](#) [JBXFD2G06MCSDSMR](#) [JBXFD2G06MCSDSR](#) [JBXFD2G07MCSDSMR](#)
[JBXFD2G08MCSDSMR](#) [JBXFD2G08MCSDSR](#) [JBXFD2G12MCSDSMR](#) [JBXFD2G16MCSDSR](#)
[JBXFD2G18MCSDSR](#) [JBXFD2G19MCSDSMR](#) [JBXFD2G19MCSDSR](#) [JBXFD2G08MCNDSMR](#) [JBXFD2G19MCSDS](#)