

# XS4P12PB370

inductive sensor XS4 M12 - L52mm - PPS -  
Sn4mm - 12..48VDC - cable 2m



Product availability: Non-Stock - Not normally stocked in distribution facility



## Main

|                                    |                                                         |
|------------------------------------|---------------------------------------------------------|
| Range of product                   | OsiSense XS                                             |
| Series name                        | General purpose                                         |
| Sensor type                        | Inductive proximity sensor                              |
| Device application                 | -                                                       |
| Sensor name                        | XS4                                                     |
| Sensor design                      | Cylindrical M12                                         |
| Size                               | 52 mm                                                   |
| Body type                          | Fixed                                                   |
| Detector flush mounting acceptance | Non flush mountable                                     |
| Material                           | Plastic                                                 |
| Type of output signal              | Discrete                                                |
| Wiring technique                   | 3-wire                                                  |
| [Sn] nominal sensing distance      | 0.16 in (4 mm)                                          |
| Discrete output function           | 1 NC                                                    |
| Output circuit type                | DC                                                      |
| Discrete output type               | PNP                                                     |
| Electrical connection              | Cable                                                   |
| Cable length                       | 6.56 ft (2 m)                                           |
| [Us] rated supply voltage          | 12...48 V DC with reverse polarity protection           |
| Switching capacity in mA           | <= 200 mA DC with overload and short-circuit protection |
| IP degree of protection            | IP68 double insulation conforming to IEC 60529          |

## Complementary

|                          |                             |
|--------------------------|-----------------------------|
| Thread type              | M12 x 1                     |
| Detection face           | Frontal                     |
| Front material           | PPS                         |
| Enclosure material       | PPS                         |
| Operating zone           | 0...0.13 in (0...3.2 mm)    |
| Differential travel      | 1...15% of Sr               |
| Cable composition        | 3 x 0.34 mm <sup>2</sup>    |
| Wire insulation material | PvR                         |
| Status LED               | 1 LED (yellow) output state |
| Supply voltage limits    | 10...58 V DC                |
| Switching frequency      | <= 5000 Hz                  |
| Voltage drop             | <= 2 V (closed              |
| Current consumption      | 0...10 mA (no-load)         |
| Delay first up           | <= 10 ms                    |
| Delay response           | <= 0.1 ms                   |
| Delay recovery           | <= 0.1 ms                   |
| Marking                  | CE                          |
| Threaded length          | 1.65 in (42 mm)             |
| Height                   | 0.47 in (12 mm)             |

|                |                        |
|----------------|------------------------|
| Length         | 2.05 in (52 mm)        |
| Product weight | 0.14 lb(US) (0.065 kg) |

## Environment

|                                       |                                                                         |
|---------------------------------------|-------------------------------------------------------------------------|
| Product certifications                | UL<br>CSA<br>Ecolab<br>CCC                                              |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                              |
| Ambient air temperature for storage   | -40...185 °F (-40...85 °C)                                              |
| Vibration resistance                  | 25 gn, amplitude: +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6 |
| Shock resistance                      | 50 gn (duration = 11 ms) conforming to IEC 60068-2-27                   |

## Ordering and shipping details

|                       |                            |
|-----------------------|----------------------------|
| Category              | 22486 - SENSORS, PROXIMITY |
| Discount Schedule     | DS2                        |
| GTIN                  | 003389110926781            |
| Nbr. of units in pkg. | 1                          |
| Package weight(Lbs)   | 0.19                       |
| Returnability         | N                          |
| Country of origin     | FR                         |

## Offer Sustainability

|                                  |                                                                                                                                                                                                         |
|----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                                                                                                   |
| RoHS (date code: YYWW)           | Compliant - since 0812 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity |
| REACH                            | Reference not containing SVHC above the threshold                                                                                                                                                       |
| Product environmental profile    | Available                                                                                                                                                                                               |
| Product end of life instructions | Available                                                                                                                                                                                               |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                                                                                                                            |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                                                                                             |
| - - - - - Substance 2            | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.                                                                               |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                                                                                           |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

## Dimensions



(1) LED

## Minimum Mounting Distances

Side by side



e (1) 16 mm/0.63 in.

≥

Face to face



e (2) 48 mm/1.89 in.

≥

Facing a metal object



e (3) 12 mm/0.47 in.

≥

Mounted in a metal support



d ≥ 36 mm/1.42 in.

h ≥ 8 mm/0.31 in.

## Mounting



(1) Bending cable: 4 x external cable diameter

## Wiring Schemes

PNP



BU : Blue  
BN : Brown  
BK : Black

---

Performance Curves

---

Standard Steel Target : 12x12x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XS4P12PB370](#)