


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFCC


FEMALE INSULATOR, CRIMP CONTACT

CONTACT LAYOUT	02	03	04	05
FRONT SIDE VIEW				
REAR SIDE VIEW				
CONTACT				
ISO VIEW				
CONTACT	ØC	2	1.6	1.3
	ØF	2.4	1.9	1.4
	MAX. AWG	12	14	18
	MAX. CURRENT RATING (A)	30	17	15
	CONTACT RESISTANCE (mΩ)	2.5	2.5	3
INSULATOR	NUMBER OF CAVITY	2	3	4
	MAX. CURRENT RATING	30	17	14
	TEST VOLTAGE (Vrms)	2100	1700	2400
	WORKING VOLTAGE (Vdc/Vrms)	1000/700	830/560	1000/700



CONTACT TYPE : F (FEMALE)
CONTACT TERMINATION : C (CRIMP)

MATERIAL :
CONTACT: CUPRO-NICKEL
CLIP: COPPER ALLOY
INSULATOR: PEEK
FINISH:
CONTACTS : GOLD



B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	TJS 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT			
CAT NO. JBX2INSFC			
CAGE NO: 09922		SIZE: B	
CUSTOMER		SOURIAU	
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		APPROVAL	
		DRAWN: TJS 02-04-15 CHKD : EV 02-04-15 DSGN : EV 02-04-15 MFG : DH 02-04-15 QC : BB 02-04-15 DRAWING SCALE: NA DRAWING NO. REV JBX2INSFCC B 1 OF 3	

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE: mm (INCH)

THIRD ANGLE PROJECTION

TOLERANCES UNLESS OTHERWISE SPECIFIED

No. OF PLACES	mm [INCH]
ONE PLACE	±3 [±.1]
TWO PLACES	±0.5 [±.02]
THREE PLACES	±0.25 [±.010]

ANGLES±1°

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFCC

CONTACT LAYOUT		06	07	08	10
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	1.3	1.3	0.9	0.9
	ØF	1.4	1.4	1.1	1.1
	MAX. AWG	18	18	20	20
	MAX. CURRENT RATING (A)	15	15	10	10
	CONTACT RESISTANCE (mΩ)	3	3	3.5	3.5
	NUMBER OF CAVITY	6	7	8	10
	MAX. CURRENT RATING	12	11	10	8
	TEST VOLTAGE (Vrms)	1900	1500	1700	1700
INSULATOR	WORKING VOLTAGE (Vdc/Vrms)	900/630	730/500	830/560	830/560

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE				
JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT				
CAT NO.				
JBX2INSFC				
CAGE NO: 09922	SIZE: B		APPROVAL	
CUSTOMER	SOURIAU	DRAWN: TJS		02-04-15
		CHKD : EV		02-04-15
		DSGN : EV		02-04-15
		MFG : DH		02-04-15
		QC : BB		02-04-15
DRAWING SCALE: NA				
DRAWING NO.		REV		
JBX2INSFCC		B		
2 OF 3				
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM		

WWW.SOURIAU.COM

PRO-E


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFCC

CONTACT LAYOUT		12	16	18	19
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	0.7	0.7	0.7	0.7
	ØF	0.85	0.85	0.85	0.85
	MAX. AWG	22	22	22	22
	MAX. CURRENT RATING (A)	7	7	7	7
INSULATOR	CONTACT RESISTANCE (mΩ)	5	5	5	5
	NUMBER OF CAVITY	12	16	18	19
	MAX. CURRENT RATING	7	6	5.5	5
	TEST VOLTAGE (Vrms)	1700	1500	1400	1400
WORKING VOLTAGE (Vdc/Vrms)		830/560	730/500	660/460	660/460

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES ±1°			

DRAWING TITLE						
JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT						
CAT NO.						
JBX2INSFC						
CAGE NO: 09922		SIZE: B		APPROVAL		
CUSTOMER		SOURIAU			DRAWN: TJS	02-04-15
					CHKD : EV	02-04-15
					DSGN : EV	02-04-15
					MFG : DH	02-04-15
					QC : BB	02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM			DRAWING SCALE: NA	
					DRAWING NO. REV	
					JBX2INSFCC B	
					3 OF 3	

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXPC2G02FCSDSR](#) [JBXPC2G04FCSDSR](#) [JBXPC2G10FCSDSMR](#) [JBXPC2G10FCSDSR](#) [JBXPC2G12FCSDSMR](#)
[JBXPC2G19FCSDSR](#) [JBXPC2G02FCSDSMR](#) [JBXPC2G03FCSDSMR](#) [JBXPC2G03FCSDSR](#)
[JBXPC2G04FCSDSMR](#) [JBXPC2G05FCSDSMR](#) [JBXPC2G05FCSDSR](#) [JBXPC2G06FCSDSMR](#)
[JBXPC2G06FCSDSR](#) [JBXPC2G07FCSDSMR](#) [JBXPC2G07FCSDSR](#) [JBXPC2G08FCSDSMR](#) [JBXPC2G08FCSDSR](#)
[JBXPC2G12FCSDSR](#) [JBXPC2G16FCSDSM](#) [JBXPC2G16FCSDSMR](#) [JBXPC2G16FCSDSR](#) [JBXPC2G18FCSDSMR](#)
[JBXPC2G18FCSDSR](#) [JBXPC2G19FCSDSMR](#)