




THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

C

B

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.



ACCOMMODATES			
PINS	REF. DWG.	SOCKETS	REF. DWG.
RM20M-12	SD50141	RC20M-12	SD50141
RM20M-13	SD50141	RC20M-13	SD50141
RM16M-23	SD50140	RC16M-23	SD50140
RM24M-9	SD50142	RC24M-9	SD50142
SM20M-1	SD52182	SC20M-1	SD52184
SM24M-1	SD52182	SC24M-1	SD52184
RMDX60-2	SC57643	RCDX60-2	SC57642

LINEAR MEASURE:			INCH (mm)
THIRD ANGLE PROJECTION			
			
TOLERANCES			
UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	INCH [mm]		
ONE PLACE	$\pm .1$ (± 3)		
TWO PLACES	$\pm .02$ (± 0.5)		
THREE PLACES	$\pm .010$ (± 0.25)		
ANGLES $\pm 1^\circ$			

NOTES:

1. MATERIAL :
BODY - GLASS FILLED PHENOLIC, PER MIL-M-14F TYPE MFH.
GUIDE PINS - STAINLESS STEEL.
GUIDE SOCKETS - STAINLESS STEEL.
JACKSCREW - STAINLESS STEEL.
2. CLOSED ENRTY SOCKET WILL NOT ALLOW ENTRANCE OF OVERSIZE
PIN OR INSPECTION PROBE ASSURING POSITIVE CONTACT PRESSURE.

4 PINS AND SOCKETS ARE INETERCHANGEABLE WITH RECEPTACLE AND PLUG SHOWN. SUBMINIATURE COAXIAL CONTACTS ARE NOT INTERCHANGEABLE. PINS MUST BE USED WITH THE RECEPTACLE AND SOCKET WITH PLUG.

J	REVISED PER ECN 11850	SKV 11-10-12	SSF 11-10-12
H	REVISED PER ECN 11804	CJM 09-17-12	SDH 09-17-12
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE		152 PLACE PANEL ASSEMBLY	
CAT NO.		MB152P/R-4	
CAGE NO: 09922	SIZE: C	APPROVAL 	DRAWN: CJM 09-14-12
 CUSTOMER			CHKD : TM 09-14-12
			DSGN : XXX mm-dd-yy
			MFG : DH 09-14-12
			QC : BB 09-14-12
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		DRAWING SCALE: 1:1	
		DRAWING NO.	REV
		SE54872	J
www.souriau.com		1 OF 2	

D

C

B

A

DWG. NO.

SE54872

- NOTES:
1. MATERIAL :
BODY - GLASS FILLED PHENOLIC, PER MIL-M-14F TYPE MFH.
GUIDE PINS - STAINLESS STEEL.
GUIDE SOCKETS - STAINLESS STEEL.
JACK SCREW - STAINLESS STEEL.
2. CLOSED ENRTY SOCKET WILL NOT ALLOW ENTRANCE OF OVERSIZE
PIN OR INSPECTION PROBE ASSURING POSITIVE CONTACT PRESSURE.

3
4




PINS AND SOCKETS ARE INETERCHANGEABLE WITH RECEPTACLE AND PLUG SHOWN. SUBMINIATURE COAXIAL CONTACTS ARE NOT INTERCHANGEABLE. PINS MUST BE USED WITH THE RECEPTACLE AND SOCKET WITH PLUG.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

C

B

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.



LINEAR MEASURE:	
INCH	INCH [mm]
THIRD ANGLE PROJECTION	
TOLERANCES UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	INCH [mm]
ONE PLACE	±.1 [±3]
TWO PLACES	±.02 [±0.5]
THREE PLACES	±.010 [±0.25]
ANGLES ±1°	

DRAWING TITLE			
152 PLACE PANEL ASSEMBLY			
CAT NO. MB152P/R-4			
CAGE NO: 09922		SIZE: C	
CUSTOMER		 www.souriau.com	APPROVAL
			DRAWN: CJM 09-14-12 CHKD : TM 09-14-12 DSGN : XXX mm-dd-yy MFG : DH 09-14-12 QC : BB 09-14-12 DRAWING SCALE: 3:2 DRAWING NO. REV SE54872 J
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		2 OF 2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[MB152P-4](#) [MB6P-6](#) [MB6P-3](#) [MB24P-5](#) [MB6R-3](#) [MB6R-5](#) [MB6P-3P5](#)