


Rack and panel connectors



SN 253 SN 353

Descriptions

- Rack & panel floating coaxial connector compensating for misalignment of ± 1 mm
- Available in solder or crimp version
- Printed circuit floating receptacle

SN 253

- Rack & panel contact coaxial connector, solder type

SN 353

- Rack & panel coax connector, crimp type



Applications

- Civil & military aircraft (instrument panel)
- Defence (interface pylon/munition)

Technical features

SN 253

Mechanical

- Shell : copper alloy
- Plating : gold, silver or nickel
- Insulator : black polyamid
- Solder contacts : copper alloy
- Plating : gold with nickel under plating

Climatics

- Operating temperature : -55°C +85°C

Electrical

- Voltage rating : 500 V
- Contact resistance : $< 8 \text{ m}\Omega$
- Insulation resistance : $> 5000 \text{ M}\Omega$
- Contact rating :
 - 7,5 A Max
 - 5 A nominal

Others

- Intermateable with SN 353 connector serie
- Mass : 0,60 g

SN 353

Mechanical

- Shell : copper alloy
- Plating : nickel
- Insulator : polyamid and black epoxy
- Removable contacts : copper alloy
- Plating : gold with nickel

Climatics

- Operating temperature : -55°C +85°C

Electrical

- Voltage rating : 500 V
- Contact resistance : $< 8 \text{ m}\Omega$
- Insulation resistance : $> 5000 \text{ M}\Omega$
- Contact rating :
 - 7,5 A Max
 - 5 A nominal

Others

- Intermateable with SN 253
- Mass : 5,5 g

For further information, please consult the customer drawing and technical specifications


Rack and panel connectors




Dimensions




SN 253S



SN 353S



SN 253P



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[SN253S](#) [SN253P](#)