

DWG. NO.

25A102

MATERIAL:


BODY: BRASS PER ASTM B 16
CONTACT: BERYLLIUM COPPER PER ASTM B 196
INSULATOR: PTFE FLUOROCARBON, ASTM-D1710

FINISH:

BODY: PROPRIETARY BRIGHT NICKLE (IP23)
CONTACT: GOLD PLATE PER ASTM B 488

IMPEDANCE:

FREQUENCY RANGE: 50/75 OHMS
VSWR: DC TO 1 GHZ
VOLTAGE RATING: 1.5 MAX
INSULATION RESISTANCE: 500 VRMS
CONTACT RESISTANCE: 5,000 MEGOHMS
CENTER: 2.5 MILLIOHMS MAX.
DUTER: 0.3 MILLIOHMS MAX.
CONNECTOR MEETS M39012



REV	DESCRIPTION	BY	DATE	CHKD	DATE
B	REDRAWN - SOURIAU FORMAT	DS	9-29-04	RGL	9-29-04

DRAWING TITLE

50 OHM "N" PLUG TO 75 OHM "N" JACK

CAT NO.

25A102-1

LINEAR MEASURE:	(INCH mm)	(INCH mm)
THIRD ANGLE PROJECTION		



TOLERANCES

UNLESS OTHERWISE SPECIFIED

NO. OF PLACES INCH [mm]

ONE PLACE ±.1 [±3]

TWO PLACES ±0.02 [±.5]

THREE PLACES ±0.010 [±.25]

ANGLES±1°

CAGE NO.: 09922

SIZE: A

CUSTOMER

INTERPRET THIS DRAWING
IN ACCORDANCE WITH
ASME Y14.5M - 1994



SOURIAU
Connection Technology

www.souriau.com

APPROVAL

DRAWN:	DS	9-28-04
CHKD:	RGL	9-28-04
DSGN:		
MFG:		
QC:		

DRAWING SCALE: N/A
DRAWING NO. REV

25A102

B

1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Souriau:](#)

[25A102-1](#)