

UTGX0---P

UTGX0---S

SEALING
CONDITIONS

PANEL CUT OUT
DEFINITION




Sealing in MATED conditions with COUNTERPART:

- IP68 1 bar during 1 week: immersion under 10 m of water. (IEC 60529)
- IP69K : exposure to high pressure water of cleaning equipement(DIN 40050)

Sealing in MATED conditions with COUNTERPARTand UNMATED conditions:

- IP68 1 bar during 1 week: immersion under 10 m of water. (IEC 60529)
- IP69K : exposure to high pressure water of cleaning equipement(DIN 40050)

PANEL CUT OUT DEFINITION						PANEL THICKNESS
SHELL SIZE	±0.1	REAR mounting	FRONT mounting	±0.15		
		±0.1				
	ØP	ØQ		R	S	MAX
10	3.2	17.9	15.2	18.3	18.3	2.8
12		22.3	18.3	20.6	20.6	
14		25.1	21.5	23.0	23.0	



SHELL SIZE	±0.4	±0.2	±0.1	±0.2	±0.2	±0.2	MAX		MIN / MAX				MAX			THREAD CLASS 2A	±30% (g.)
	A	B	ØC	D	E	ØF	G	H	J1	J2	K1	K2	L	M	N		MASS
10	23.8	18.26	3.2	11.35	2.3	15.2	19.5	12.1	15.8 / 17.7	18.1/ 20	15.8/ 17.7	18.1/ 20	32.3	11.5	11.5	9/16-24 UNEF	6
12	26.2	20.62				19.15			*	*	*	*				11/16-24 UNEF	10
14	28.6	23.01				22.31			*	*	*	*				13/16-20 UNEF	13







* -1mm FOR LAYOUT 12D14

SIDE VIEW FOR EACH VERSION


UTGX0-----

UTGX0--D---


UTGX0--E---



COMMON QUOTES FOR ALL VERSION



SHELL RECEPTACLE



SCALE 2/1

MATERIAL :

- SHELL : PA UL94 V0, UL746C F1 Black color
- 3 LOCKING PINS RING : Nickel plated Brass + stainless steel.
- INSERT (UTGX0-----) : PA UL94 V0, UL746C F1 Black color
- INSERT (UTGX0--D/E---) : Polychloroprene
- CONTACTS: brass + coated depending on P/N

PERFORMANCE CHARACTERISTICS :

Operating temperature: -40°C up to 105°C
Insulation resistance: 5000 MΩmin under 500V
Corrosion salt spray: 500 hours
Durability: 500 matings and unmatings
Sealing conditions: SEE TABLE

NOTA:

- 1- Contact to be ordered separately for version UTGX0----- : refer to corresponding catalogue.
- 2- Insert arrangement refer to:
 - UTO-CONTACT-L-C02 (Female insulator)
 - UTO-DHP-003-C01 (Female insulator #20)
 - UTO-DHP-002-C01 (Female insulator #16)
 - UTO-CONTACT-L-C01 (Male insulator)
 - UTO-DHP-003-C01 (Male insulator #20)
 - UTO-DHP-001-C01 (Male insulator #16)
 - C144-UTS1-A (HiSeal Version)

Country Jurisdiction & Control List	
FR	NOT LISTED

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

P/N : CROSS REF TABLE

BASIC SERIES	UTGX 0 14 D 19 P -	* P/N for example
SHELL TYPE	0 Square flange receptacle	
SHELL SIZE	10 12 14	
TYPE OF LAYOUT	Standard layout (No digit) D : HISEAL Dispolder contacts E : HISEAL Handsolder contacts	
INSERT ARRANGEMENT	See NOTA 2	ORIENTATIONS Normal (no digit) W.X.Y.Z
TYPE OF CONTACTS	P: MALE S: FEMALE	

B	14/02/2020	-Update drawing	25253J
ISS	DATE	Latest modification - by: J.FEURPRIER	MOD N°
Designed by: PE.LANDAIS Date:10/05/2019		CUSTOMER DRAWING	
TITLE		SQUARE FLANGE RECEPTACLE T0 - SIZE 10 12 14 - Standard and Hiseal version UTGX CONNECTOR	
Scale	3/2	Dimensions in mm General Linear Tolerances: ±0.2	NPRDS / PROJECT GBB
SOURIAU Connection Technologies		www.souriau.com	This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A2	SOURIAU DRG N° UTGX-0001A-C	
			SHEET 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[UTGX0103P](#) [UTGX014D7P](#) [UTGX014E12P](#) [UTGX014D19P](#) [UTGX01419P](#) [UTGX0142G1P](#) [UTGX0147P](#)
[UTGX012E8P](#) [UTGX01412P](#) [UTGX012D4P](#) [UTGX012E10S](#) [UTGX0124P](#) [UTGX0128P](#) [UTGX01210P](#) [UTGX0104P](#)
[UTGX0106P](#) [UTGX010D6P](#) [UTGX0104PW](#) [UTGX0104SW](#) [UTGX0106PW](#) [UTGX0106SW](#) [UTGX010D6PW](#)
[UTGX010D6SW](#) [UTGX010D7PW](#) [UTGX010D7SW](#) [UTGX010D98PW](#) [UTGX010D98PX](#) [UTGX010D98PY](#)
[UTGX010D98PZ](#) [UTGX010D98SW](#) [UTGX010D98SX](#) [UTGX010D98SY](#) [UTGX010D98SZ](#) [UTGX010E6PW](#)
[UTGX010E6SW](#) [UTGX010E7PW](#) [UTGX010E7SW](#) [UTGX010E98PW](#) [UTGX010E98PX](#) [UTGX010E98PY](#)
[UTGX010E98PZ](#) [UTGX010E98SW](#) [UTGX010E98SX](#) [UTGX010E98SY](#) [UTGX010E98SZ](#) [UTGX01210PW](#)
[UTGX01210PX](#) [UTGX01210PY](#) [UTGX01210PZ](#) [UTGX01210SW](#) [UTGX01210SX](#) [UTGX01210SY](#) [UTGX01210SZ](#)
[UTGX0128PW](#) [UTGX0128SW](#) [UTGX012D10PW](#) [UTGX012D10PX](#) [UTGX012D10PY](#) [UTGX012D10PZ](#)
[UTGX012D10SW](#) [UTGX012D10SX](#) [UTGX012D10SY](#) [UTGX012D10SZ](#) [UTGX012D14PW](#) [UTGX012D14SW](#)
[UTGX012D3PY](#) [UTGX012D3SY](#)