

SIDE VIEW FOR EACH VERSION

COMMON QUOTES FOR ALL VERSION

MATERIAL :

- SHELL : PA UL94 V0, UL746C F1 Black color
- 3 LOCKING PINS RING : Nickel plated Brass + stainless Steel
- INSERT (UTGX7-----) : PA UL94 V0, UL746C F1
- INSERT (UTGX7--D/E---) : Polychloroprene
- NUT : Aluminium alloy + Anodic oxidation
- O'RING : Nitril
- CONTACTS : brass + coated depending on P/N


PERFORMANCE CHARACTERISTICS :

Operating temperature: -40°C up to 105°C
Insulation resistance: 5000 MΩmin
Corrosion salt spray: 500 hours
Durability: 500 matings and unmatings
Sealing conditions: SEE TABLE


NOTA:

- 1- Contact to be ordered separately for version UTGX7----- : refer to corresponding catalogue.
- 2- Insert arrangement refer to:
 - UTO-CONTACT-L-C02 (Female insulator)
 - UTO-DHP-003-C01 (Female insulator #20)
 - UTO-DHP-002-C01 (Female insulator #16)
 - UTO-CONTACT-L-C01 (Male insulator)
 - UTO-DHP-003-C01 (Male insulator #20)
 - UTO-DHP-001-C01 (Male insulator #16)
 - C144-UTS1-A (HiSeal Version)



UTGX7-----P







UTGX7--D---



UTGX7--E---



UTGX7-----S




SEALING
CONDITION

Sealing in MATED conditions with COUNTERPART:
-IP68 1 bar during 1 week: immersion under 10 m of water. (IEC 60529)
-IP69K : exposure to high pressure water of cleaning equipment(DIN 40050)


Sealing in MATED conditions with COUNTERPART and UNMATED conditions:
-IP68 1 bar during 1 week: immersion under 10 m of water. (IEC 60529)
-IP69K : exposure to high pressure water of cleaning equipment(DIN 40050)

Sealing in MATED conditions with COUNTERPART and UNMATED conditions:
-IP68 1 bar during 1 week: immersion under 10 m of water. (IEC 60529)
-IP69K : exposure to high pressure water of cleaning equipment(DIN 40050)

PANEL CUT OUT and DRILLING
PATTERN DEFINITION



CONNECTOR FRONT VIEW : SPECIFICATION 32



Country	Jurisdiction & Control List
FR	NOT LISTED

SOURIAU shall not be liable for any non-conformity or damage due to a use of the Products which does not comply with the Specifications issued by either of the Parties or by a third party (professional recommendation, technical notice.)

P/N : CROSS REF TABLE

BASIC SERIES	UTGX 7 14 D 19 P - --	* P/N for example
SHELL TYPE	7 Jam nut receptacle	
SHELL SIZE	10 12 14	
TYPE OF LAYOUT	Standard layout (No digit) D : HISEAL Dispolder contacts E : HISEAL Handsolder contacts	
INSERT ARRANGEMENT	See NOTA 2	
		SPECIFICATION Ø : Without Hold on 32: With Hold on (see definition in table)
		ORIENTATIONS Normal (no digit) W.X.Y.Z
		TYPE OF CONTACTS P: MALE S: FEMALE

SHELL SIZE	±0.2	±0.2	MAX	±0.2	±0.3	±0.2	MAX	±0.25	MIN / MAX	MAX	±0.25	MIN / MAX	±0.1	±0.15	±2	±0.1	±0.1	±0.1	±0.1	±0.1	UNEF CLASS 2A	±20% (g.)
	A	B	C	ØD	E	F	G	H	J	K	L	M	N	ØP	Q	R	S	T	U	ØV	THREAD	MASS
10	27.00	22.15		15.20									16.6	17.9		3.98	9.85	9.20	5.31		11/16 24	10
12	31.75	27.15	18.1	19.15	2.2	24.5	15.2	6.57	11.5/13.4 *	7.8	6.57	11.5/13.4 *	21.3	22.7	3	4.92	12.17	11.37	6.56	3.1	7/8 20	15
14	34.90	30.20		22.31									24.4	25.9		5.29	13.10	12.23	7.06		1"20	20

* -1mm FOR LAYOUT 12D14

B	14/02/2020	Update drawing	25253J
ISS	DATE	Latest modification - by: J.FEURPRIER	MOD N°
Designed by: PE.LANDAIS Date:10/05/2019		CUSTOMER DRAWING	
TITLE		JAM NUT RECEPTACLE - SIZE 10 12 & 14 - Standard and Hiseal version	
		UTGX CONNECTOR	
Scale	3/2	Dimensions in mm General Linear Tolerances: ±0.2	NPRDS / PROJECT GBB
SOURIAU Connection Technologies		www.souriau.com	This document is the property of SOURIAU It must not be reproduced or communicated without permission
FORMAT	A2	SOURIAU DRG N° UTGX-0002A-C	
			SHEET 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[UTGX7102W2P](#) [UTGX7102W2S](#) [UTGX7103P](#) [UTGX7103S](#) [UTGX7103W3P](#) [UTGX714E7S](#) [UTGX714E18S](#)
[UTGX714E19P](#) [UTGX714E19S](#) [UTGX714E5P](#) [UTGX714E5S](#) [UTGX714E7P](#) [UTGX714D7S32](#) [UTGX714E12P](#)
[UTGX714E12S](#) [UTGX714E15P](#) [UTGX714E15S](#) [UTGX714E18P](#) [UTGX714D5P32](#) [UTGX714D5S](#) [UTGX714D5S32](#)
[UTGX714D7P](#) [UTGX714D7P32](#) [UTGX714D7S](#) [UTGX714D18S32](#) [UTGX714D19P](#) [UTGX714D19P32](#)
[UTGX714D19S](#) [UTGX714D19S32](#) [UTGX714D5P](#) [UTGX714D15P32](#) [UTGX714D15S](#) [UTGX714D15S32](#)
[UTGX714D18P](#) [UTGX714D18P32](#) [UTGX714D18S](#) [UTGX71492S](#) [UTGX714D12P](#) [UTGX714D12P32](#)
[UTGX714D12S](#) [UTGX714D12S32](#) [UTGX714D15P](#) [UTGX7147P](#) [UTGX7147PSEK9](#) [UTGX7147S](#) [UTGX7148P](#)
[UTGX7148S](#) [UTGX71492P](#) [UTGX71412P](#) [UTGX71412S](#) [UTGX71419P](#) [UTGX71419S](#) [UTGX7142G1P](#)
[UTGX7142G1S](#) [UTGX712E3P](#) [UTGX712E3S](#) [UTGX712E4P](#) [UTGX712E4S](#) [UTGX712E8P](#) [UTGX712E8S](#)
[UTGX712E10P](#) [UTGX712E10S](#) [UTGX712E14P](#) [UTGX712E14S](#) [UTGX712E2P](#) [UTGX712E2S](#) [UTGX712D4S](#)
[UTGX712D4S32](#) [UTGX712D8P](#) [UTGX712D8P32](#) [UTGX712D8S](#) [UTGX712D8S32](#) [UTGX712D3P](#) [UTGX712D3P32](#)
[UTGX712D3S](#) [UTGX712D3S32](#) [UTGX712D4P](#) [UTGX712D4P32](#) [UTGX712D14S](#) [UTGX712D14S32](#) [UTGX712D2P](#)
[UTGX712D2P32](#) [UTGX712D2S](#) [UTGX712D2S32](#) [UTGX712D10P](#) [UTGX712D10P32](#) [UTGX712D10S](#)
[UTGX712D10S32](#) [UTGX712D14P](#) [UTGX712D14P32](#) [UTGX71210S](#) [UTGX7124P](#) [UTGX7124S](#) [UTGX7128P](#)
[UTGX7128PSEK9](#) [UTGX7128S](#) [UTGX710E6S](#) [UTGX710E7P](#) [UTGX710E7S](#) [UTGX710E98P](#)