




A.14: Valid é




NOTES

MATERIALS
SHELL : BLACK POLYAMID
COUPLING / BACKSHELL O'RING : LUBRICATED RED SILICON
LOCKING LATCH : STAINLESS STEEL
BACKSHELL BODY : BLACK POLYAMID
FLAT SEAL : NBR OR CR
CABLE GLAND BODY AND NUT : BLACK POLYAMID
CABLE GLAND SEAL : CR
CONTACT BODY : BRASS ALLOY
CONTACT CLIP : COPPER ALLOY
SCREW : STAINLESS STEEL

PERFORMANCES CHARACTERISTICS

MECHANICAL		
TEMPERATURE CLASS	IEC61984/UL1977	-40°C TO 105°C
DURABILITY	IEC61984	500 MATE / UNMATE CYCLES
SEALING IN MATED CONDITIONS	IEC60529	IP68 1BAR DURING 1WEEK
	DIN40050	IP69K
OPEN FACE SEALING	IEC60529	WITH SEALED CONTACT REF. R*M25* CONTACTS 4
POLLUTION DEGREE	IEC61984	MIN 1000H EXPOSURE
CORROSION SALT SPRAY		INSULATING MATERIAL : VO LEVEL
FLAMMABILITY	UL94	
SCOOP PROOF		
ELECTRICAL		
TOUCH PROOF	IEC60529	IP2X
WITHSTANDING VOLTAGE		2200VAC DURING 1 MIN
GROUND POSITION		FIRST MATE LAST BREAK
POWER POSITION MARKED "L" AND "N"		
NOMINAL CURRENT	UL1977	16A WITH AWG14 WIRE / 13A WITH AWG16 WIRE
NOMINAL CURRENT	IEC61984	16A WITH 2.5MM² WIRE / 13A WITH 1.5MM² WIRE
NOMINAL VOLTAGE	UL1977	277V
NOMINAL VOLTAGE	IEC61984	250VAC 4KV 4 FOR CLASS II EQUIPMENT
	IEC61984	500VAC 6KV 4 FOR CLASS I EQUIPMENT
NOMINAL CURRENT AND VOLTAGE FOR CBC USE	UL1977	277V 13A WITH AWG14/16 WIRES FOR CBC USE
	IEC61984	250VAC 13A 4KV 4 FOR CBC USE
CONTROL POSITION MARKED "1" AND "2"		48V , 1A, FREQUENCY UP TO 100 Mhz
REGULATION :		
ROHS COMPLIANT		

- COUNTERPART REFERENCE UTL RECEPTACLE
- CONNECTORS ARE DELIVERED AS PRE-ASSEMBLED KIT
- CONTACTS ARE INCLUDED INTO THE KIT
- UNIT IN MM
- WIRE INSULATOR MAX DIAMETER : Ø4,5mm / 1.5mm² SECTION
- CAPACITY C : Ø10mm-Ø17mm
- CONTACT SCREW TIGHTENING TORQUE : 0.4 N.m MAX
- SCREWDRIVER DIMENSIONS : 2mm MAX WIDTH
- TIP SCREWDRIVER FOR SLOTTED HEAD SCREW
- FOR WIRING INSTRUCTION SEE BT330



P/N : UTL6JC145SSCR

A	24/01/2017	First edition		24328PR
ISS	DATE	Latest modification - by: --		MOD N°
Designed by:		R.M.	Date: 1 24/01/2017	CUSTOMER DRAWING
TITLE		FEMALE PLUG TYPE 6 SIZE 14 LAYOUT 5 SCREW TIGHTENING CTS		
		UTL CONNECTOR		
Scale	1/1		General linear Tolerances: ± 0.2	NPRDS / PROJECT BE151304A
SOURIAU		WWW.SOURIAU.COM		This document is the property of SOURIAU. It must not be reproduced or communicated without permission.
FORMAT	A2	SOURIAU DRG N° UTL1-0081A-C		SHEET 1 / 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

UTL6JC145SSCR