


NOTES:

1. MAX. MOUNTING TORQUE = 4 lb-in.
2. HARDWARE IS INCLUDED.
3. THIS IS A LEAD FREE PRODUCT.
4. MAX. REFLOW IS 245°C FOR 5 SEC.



LEAD FINISH: TIN/SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	1000pF $\begin{smallmatrix} -0 \\ +100\% \end{smallmatrix}$
TEMP. RANGE	-55°C TO +125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	125°C 100 VDC -----
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
30	11
100	20
300	28
1 GHz	28
10 GHz	28

SCHEMATIC



MARKING:


PART: SF 108

54F-713-108

DATE CODE

QTY./BAG

(200/BAG MAX.)

				00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 <p>FAIRVIEW PENNSYLVANIA</p>	
				CN 29233-CPD	CHANGE NOTICE	Fractions $\pm 1/64$ Dec. .xx± Dec. .xxx±.010 Angles $\pm 0^{\circ} 30'$		
						CODE IDENT. NO. DLSP2	Dwn. KAUFFMAN	Description FT
							DATE 7-11-06	RESIN SEAL FILTER
							Engr. STRUCHEN	
							Scale NONE	54F-713-108

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[54F-713-108](#)