



NOTES:

1. SUGGESTED MOUNTING HOLE = $\phi.191[4.86]$
2. PRE FLATTEN/NOTCH DIMENSIONS
TOP: $.323 \pm .010$
3. SUPPLY PREFORM AS HARDWARE.



LEAD FINISH:	SOLDER
BUSHING FINISH:	SILVER
CAPACITANCE	1000pF +100/-0%
TEMP. RANGE	-55°C TO 125°C
CURRENT	25 AMP MAX.
WORKING VOLTAGE	85°C VDC MAX. 125°C 500VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
10	N/A
100	N/A
1 GHz	N/A
10 GHz	N/A


SCHEMATIC



MARKING:

PART: NONE
BAG:
54F-794-035
DATE CODE
QTY./BAG (200 MAX.)

02	01	00	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED
CN. 56454-ENG	CN. 37800-ENG	CN. 34636-CPD	CHANGE NOTICE	Fractions $\pm 1/64$
				Dec. $.xx \pm$
				Dec. $.xxx \pm .015$
				Angles $\pm 0^\circ 30'$
				CODE IDENT. NO. DLSP2



FAIRVIEW
PENNSYLVANIA

Dwn. KAUFFMAN	Description FT
Date 10-27-10	CERAMIC FILTER
Engr. S. PETERS	
Scale NONE	54F-794-035

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[54F-794-035](#)