




- NOTES:
1. SUGGESTED MOUNTING HOLE = $\phi.191[4.86]$
 2. PRE FLATTEN/NOTCH DIMENSIONS
TOP: $.323 \pm .010$
 3. THIS PRODUCT IS LEAD FREE.
 4. MAX REFLOW TEMP IS 245°C FOR 5 SECONDS.
 5. PREFORM IS SUPPLIES AS HARDWARE.

LEAD FINISH	SILVER
BUSHING FINISH	SILVER
CAPACITANCE	1000pF + 100 / -0%
TEMP. RANGE	-55°C TO +125°C
CURRENT	25 AMPS MAX.
WORKING VOLTAGE	85°C VCD MAX. 125°C 250 VDC MAX
DC RESISTANCE	.01 ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHZ	I.L. (db)
1	N/A
100	15
300	25
1 GHz	35
10 GHz	40
SCHEMATIC 	
MARKING: PART: NONE BAG: 54F-803-017 LOT # _____ DATE CODE _____ QTY/BAG (50 MAX.)	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[54F-803-017](#)